



CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes




ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-4 @20°C	0.021 ohms ±20%
INDUCTANCE	2-4 100kHz, 100mV, Ls	60µH ±10%
SATURATION CURRENT	2-4 20% rolloff from initial	6.8A
DIELECTRIC	2-core 625VAC, 1 second	500VAC, 1 minute



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.



Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability. Marking method, font and color may vary on preproduction samples.

DFM	SP	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]	DRAWING TITLE	PART NO.
DATE	1/21/2021	Method: Tray		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	INDUCTOR	750319584
ENG	EJK	PKG-0734				
REV.	01					
DATE	2/26/2021	www.we-online.com/midcom				SPECIFICATION SHEET 1 OF 1