

# DESIGN KIT

## WR-MPC3 Micro Power Connector



### 662 0xx 211 22

Dual Row Male Vertical Headers

### 662 0xx 210 22

Dual Row Male Right Angled Headers with Snap-in Plastic Pegs

Packaging: Tube  
No. of pins: xx = 02 – 24  
Pitch: 3.00 mm

### 662 pxx 236 022

SMT Dual Row Male Right Angled Headers with Snap-in Plastic Pegs

Packaging: p = 0: Tube  
No. of pins: xx = 02 – 24

Packaging: p = 1: Tape & Reel  
No. of pins: xx = 02 – 16  
Pitch: 3.00 mm

### 662 0xx 218 22

Dual Row Male Plug Housings with Panel Mounting Ears

### 662 0xx 113 322

Dual Row Female Receptacle Housings

Packaging: Bag  
No. of pins: xx = 02 – 24  
Pitch: 3.00 mm

### 662 0xx 111 22

Single Row Male Vertical Headers

### 662 0xx 110 22

Single Row Male Right Angled Headers with Snap-in Plastic Pegs

Packaging: Tube  
No. of pins: xx = 02 – 12  
Pitch: 3.00 mm

### 662 1xx 136 022

SMT Single Row Male Right Angled Headers with Snap-in Plastic Pegs

Packaging: Tape & Reel  
No. of pins: xx = 02 – 06  
Pitch: 3.00 mm

### 662 pxx 235 922

SMT Dual Row Male Vertical Headers with Through Hole Retention Clips

Packaging: p = 0: Tube  
No. of pins: xx = 02 – 24

Packaging: p = 3: Tape & Reel with Cap  
No. of pins: xx = 02 – 16

Pitch: 3.00 mm

### 662 pxx 230 822

SMT Dual Row Male Right Angled Headers with Through Hole Retention Clips

Packaging: p = 0: Tube  
No. of pins: xx = 02 – 24

Packaging: p = 1: Tape & Reel  
No. of pins: xx = 02 – 16

Pitch: 3.00 mm

### 662 p0x 137 22 (DEC)

AWG#24–20 Male (x = 2) / Female (x = 1) / Low Force Female (x = 3) Crimp Terminals

AWG#30–26 Male (x = 5) / Female (x = 4) / Low Force Female (x = 6) Crimp Terminals

Packaging: p = 0: 10 kpcs Reel  
p = 0 & DEC: 100 loose pcs in Bag  
p = 1: 1 kpcs Reel

### 662 3xx 135 922

SMT Single Row Male Vertical Headers with Through Hole Retention Clips

Packaging: Tape & Reel with Cap  
No. of pins: xx = 02 – 06

Pitch: 3.00 mm

### 662 1xx 130 822

SMT Single Row Male Right Angled Headers with Through Hole Retention Clips

Packaging: Tape & Reel  
No. of pins: xx = 02 – 06

Pitch: 3.00 mm

### 662 pxx 231 822

SMT Dual Row Male Vertical Headers with SMT Solder Tabs

Packaging: p = 0: Tray  
No. of pins: xx = 02 – 24

Packaging: p = 3: Tape & Reel with Cap  
No. of pins: xx = 02 – 24

Pitch: 3.00 mm

### 662 pxx 231 722

SMT Dual Row Male Right Angled Headers with SMT Solder Tabs

Packaging: p = 0: Tray  
No. of pins: xx = 02 – 24

Packaging: p = 1: Tape & Reel  
No. of pins: xx = 02 – 24

Pitch: 3.00 mm

### 662 0xx 118 22

Single Row Male Plug Housings with Panel Mounting Ears

### 662 0xx 013 322

Single Row Female Receptacle Housings

Packaging: Bag  
No. of pins: xx = 02 – 12

Pitch: 3.00 mm

### 662 3xx 131 822

SMT Single Row Male Vertical Headers with SMT Solder Tabs

Packaging: Tape & Reel with Cap  
No. of pins: xx = 02 – 06

Pitch: 3.00 mm

### 662 1xx 145 021

SMT Single Row Male Right Angled Headers with SMT Solder Tabs

Packaging: Tape & Reel  
No. of pins: xx = 02 – 12

Pitch: 3.00 mm

EMC COMPONENTS | INDUCTORS | TRANSFORMERS | RF COMPONENTS | CIRCUIT PROTECTION | EMC SHIELDING MATERIAL | **CONNECTORS** | SWITCHES | ASSEMBLY TECHNIQUE | POWER ELEMENTS

**Important information:** Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

Please check datasheets on [www.we-online.com](http://www.we-online.com) for specifications. Würth Elektronik eiSos GmbH & Co. KG, EMC & Inductive Solutions. © 2016

[www.we-online.com](http://www.we-online.com)

All products  
ex stock!