# **USER GUIDE**

# UG016 | Thermally Conductive Insulator Pad – WE-TINS

Sebastian Mirasol-Menacho



3.5 W/m·K

White

0.25 mm

1.5 g/cm<sup>3</sup>

70 Shore A

-60 up to 200 °C

#### 1. INTRODUCTION TO WE-TINS

The WE-TINS is a thermal interface material designed to provide a robust thermal interface capable of withstanding significant compression forces while ensuring electrical insulation between contact surfaces. This makes it an ideal thermal solution where both electrical insulation and high compression force are required.

The pad's contact surfaces are composed of dry silicone rubber, which is both soft and conformable. This combination allows the pad to effectively interface with rough or uneven surfaces, ensuring thermal conductivity.

Additionally, the material's reworkable nature provides flexibility during assembly and maintenance, allowing for adjustments and repositioning without compromising performance.

The WE-TINS pad is engineered to maintain its properties under varying environmental conditions, including high temperatures and mechanical stress. This durability ensures long-term reliability and efficiency in demanding applications such as power electronics, consumer electronics, and industrial machinery.

The properties of the WE-TINS thermally conductive insulator pads can be grouped into three categories, shown in Table 1,

Material Properties

1.6 W/m·K

Pink

0.23 mm

 $2.5 \text{ g/cm}^3$ 

85 Shore A

## 2. MATERIAL SPECIFICATIONS


The thermally conductive insulator pad has two main components, shown in Figure 1:

#### Filled silicone rubber:

It provides the pad with a conformable surface that fills moderately rough contact surfaces. Due to its rubber characteristics, the contact surfaces are dry and the pads can be reworked and repositioned as needed during assembly and maintenance.

#### Fiberglass mesh:

The mesh gives the part mechanical stability under high compression forces.



Operating -60 up to 180 °C

Table 1: Material properties of WE-TINS

Table 2, and Table 3:

**Bulk Thermal** 

Conductivity

Color

Thickness

Specific Gravity

Hardness

Thermal Properties (17.25 N/cm² Compression)					
Bulk Thermal Conductivity	1.6 W/m⋅K	3.5 W/m⋅K			
Thermal Impedance	4.84 K·cm²/W	1.94 K·cm²/W			

Table 2: Thermal properties of WE-TINS

Electrical Properties					
Bulk Thermal	1.6 W/m⋅K	3.5 W/m⋅K			
Conductivity	1.0 W/111·N				
Breakdown Voltage	5.5 kV	4 kV			
Volume Resistivity	10¹⁴ Ω·cm	10¹⁴ Ω·cm			

Table 3: Electrical properties of WE-TINS

## 3. DESIGN CONSIDERATIONS

When interfacing a transistor with a cooling assembly, the most popular solutions are the use of mica for its electrically insulating properties and thermal greases that wet-out hard contact surfaces. This approach presents long term reliability issues stem from the materials themselves.

Mica is an excellent electrical insulator, however one of its main disadvantages is it is naturally brittle. This can result in total interfacial failure in designs that have to withstand vibrations and/or are susceptible to large temperature fluctuations.

Thermal pastes and greases, while providing a thin bond line thickness, suffer from the pump-out effect. Solid contact surfaces which are heating up and cooling down suffer constant expansion and contraction; over time, this pushes the interface out of the gap and degrade significantly the thermal performance of the system.

Thermally conductive insulating pads can provide a reliable alternative to the use of mica and greases.

### How to design-in the WE-TINS

Let's consider a scenario where we are interfacing a TO-220 transistor with a heatsink, as shown in Figure 2, where we want to evaluate and decide between two thermal interface strategies:




Figure 2: Design-in of WE-TINS

For this purpose, we will use thermal resistance formula:

$$R = \frac{L}{\lambda \cdot A} \tag{1}$$

Where:

- L bond line thickness
- λ thermal conductivity of the material
- A area of contact surface

#### Scenario 1

Since we are simply evaluating the thermal resistance of the interface, we can focus only on the physical and thermal properties:

Material	Thickness	Area	Thermal Conductivity
Mica	0.5 mm	289 mm <sup>2</sup>	0.45 W/m·K
Thermal Grease	0.1 mm	289 mm <sup>2</sup>	5 W/m·K

Table 4: Physical and thermal properties of Mica and Thermal Grease.

Thermal resistance of the grease:

$$R_{paste} = \frac{1 \cdot 10^{-4} \text{ m}}{5 \frac{\text{W}}{\text{mK}} \cdot 2.89 \cdot 10^{-4} \text{ m}^2} = 0.07 \frac{\text{K}}{\text{W}}$$
 (2)

Thermal resistance of the mica:

$$R_{\text{mica}} = \frac{5 \cdot 10^{-4} \text{ m}}{0.45 \frac{\text{W}}{\text{m}^{\text{K}}} \cdot 2.89 \cdot 10^{-4} \text{ m}^2} = 3.84 \frac{\text{K}}{\text{W}}$$
 (3)

To calculate the total thermal resistance of the interface, we must take into consideration both layers of thermal grease as well as the mica. This will give us the total thermal resistance of the interface:

$$R_{\text{scenario 1}} = 2 \cdot R_{\text{paste}} + R_{\text{mica}}$$
$$= 2 \cdot 0.07 \frac{K}{W} + 3.84 \frac{K}{W} = 3.98 \frac{K}{W}$$
 (4)

# UG016 | Thermally Conductive Insulating Foil – WE-TINS

#### Scenario 2

As with the previous scenario, we can focus on the physical and thermal properties of the WE-TINS insulator pad:

Material	Thickness	Area	Thermal Conductivity
WE-TINS 1.6	0.23 mm	289 mm <sup>2</sup>	1.6 W/m⋅K
WE-TINS 3.5	0.25 mm	289 mm <sup>2</sup>	3.5 W/m·K

Table 5: Physical and thermal properties of WE-TINS insulator pad

Thermal resistance of the WE-TINS 1.6 W/m·K:

$$R_{TINS 1.6} = \frac{2.3 \cdot 10^{-4} \text{ m}}{1.6 \frac{\text{W}}{\text{m} \cdot \text{K}} \cdot 2.89 \cdot 10^{-4} \text{ m}^2} = 0.49 \frac{\text{K}}{\text{W}}$$
 (5)

Thermal resistance of the WE-TINS 3.5 W/m·K:

$$R_{\text{TINS 3.5}} = \frac{2.5 \cdot 10^{-4} \text{ m}}{3.5 \frac{\text{W}}{\text{mK}} \cdot 2.89 \cdot 10^{-4} \text{ m}^2} = 0.25 \frac{\text{K}}{\text{W}}$$
 (6)

Since the lower performing 1.6 W/m·K thermally conductive insulator pad already has a lower thermal resistance than that of the first scenario, we assume:

$$R_{\text{scenario 2}} = 0.49 \frac{K}{W}$$
 (7)

#### Conclusion

Now that we have performed a preliminary assessment of both scenarios, we can conclude that a WE-TINS will have a similar, if not better, thermal performance than a combined mica and thermal grease interface. It also simplifies the assembly as the handling of pads is easier than the other interfacial solutions explored.

## 4. THERMAL PERFORMANCE

The added value that thermally conductive insulator pads bring when compared to elastomeric pads is that they can withstand higher compressive pressure. As with any gap filling thermal interface, the higher the compression, the lower the thermal resistance of the pad.

This is due to two factors:

- Reduction in bond line thickness
- Increase in contact area due to adaptation of surface roughness




Figure 3: Thermal impedance as a function of the compression force.

## 5. THERMAL MEASUREMENT SETUP

All thermal parameters mentioned in this guideline have been performed in-house following ASTM D5470 - Standard Test Method for Thermal Transmission Properties of Thermally Conductive Electrical Insulation Materials, as seen in Figure 4. The standard focuses on steady-state heat transfer conditions.

During testing, a constant heat source is applied to one side of the TIM (thermal interface material) specimen, while a cooling assembly ensures a temperature difference to create a heat flow through the material under test. This setup allows for the measurement of thermal conductivity and impedance under different temperature and mechanical conditions.




Figure 4: ASTM D5470 testing setup

## 6. INSTALLATION AND HANDLING

The correct installation of TIM is crucial for ensuring optimal thermal performance and long-term reliability of electronic devices. During installation, it is essential that the pads are clean, free from contaminants, and properly aligned with the components they are intended to cool. Proper alignment guarantees maximum surface contact, minimizing thermal resistance. Applying an appropriate amount of pressure while installing the pads is vital. Adequate pressure helps in squeezing out air pockets and ensures a tight bond between the pad, the electronic component, and the heatsink.

In order to ensure correct application, the following steps are recommended:

- The surface of the component and cooling assemblies must be clean and dry. It is recommended to use isopropyl alcohol applied with a lint-free wipe or swab to remove any particles on contact surfaces.
- Place the pad on one of the contact surfaces and hold it in place.

- **3.** Position the rest of the assembly and ensure that the pad is aligned with the profile.
- **4.** Apply the recommended compression.

## Cutting

The WE-TINS can be cut into shape with any sharp object. Laser cutting is discouraged because it can harden the edges and decrease thermal performance of the pad by increasing its hardness around the cut.

#### Reworking

If the pads are not damaged upon installation, they can be removed and used again for repositioning during assembly as long as the contact surfaces remain clean and free of any foreign particles.

# **USER GUIDE**

UG016 | Thermally Conductive Insulating Foil – WE-TINS

# 7. MODIFICATION AND PROTOTYPING SERVICE

Würth Elektronik provides a shape modification service that accompanies you from prototyping to manufacturing, offering no MOQ or tooling costs. The goal of this service is to support you from prototyping to manufacturing.

Modified shapes are performed by die-less cutting. This technique allows a knife to cut a standard sheet into any desired shape within the machine's tolerances. The parts will be delivered in bulk or on a sheet if a pressure sensitive adhesive is required.

Reach out to your Würth Elektronik representative with the following information, and they will get back to you with a personalized quotation:

- Base material
- Number of parts needed
- Technical drawing of desired part
- Any special requests you may have

**UG016a** | 2025/02/25 WÜRTH ELEKTRONIK eiSos

www.we-online.com

# UG016 | Thermally Conductive Insulating Foil – WE-TINS

#### **IMPORTANT NOTICE**

The Application Note is based on our knowledge and experience of typical requirements concerning these areas. It serves as general guidance and should not be construed as a commitment for the suitability for customer applications by Würth Elektronik eiSos GmbH & Co. KG. The information in the Application Note is subject to change without notice. This document and parts thereof must not be reproduced or copied without written permission, and contents thereof must not be imparted to a third party nor be used for any unauthorized purpose.

Würth Elektronik eiSos GmbH & Co. KG and its subsidiaries and affiliates (WE) are not liable for application assistance of any kind. Customers may use WE's assistance and product recommendations for their applications and design. The responsibility for the applicability and use of WE Products in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate and investigate, where appropriate, and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

The technical specifications are stated in the current data sheet of the products. Therefore the customers shall use the data sheets and are cautioned to verify that data sheets are current. The current data sheets can be downloaded at www.we-online.com. Customers shall strictly observe any product-specific notes, cautions and warnings. WE reserves the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services.

WE DOES NOT WARRANT OR REPRESENT THAT ANY LICENSE,

EITHER EXPRESS OR IMPLIED, IS GRANTED UNDER ANY PATENT RIGHT, COPYRIGHT, MASK WORK RIGHT, OR OTHER INTELLECTUAL PROPERTY RIGHT RELATING TO ANY COMBINATION, MACHINE, OR PROCESS IN WHICH WE PRODUCTS OR SERVICES ARE USED. INFORMATION PUBLISHED BY WE REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE A LICENSE FROM WE TO USE SUCH PRODUCTS OR SERVICES OR A WARRANTY OR ENDORSEMENT THEREOF.

WE products are not authorized for use in safety-critical applications, or where a failure of the product is reasonably expected to cause severe personal injury or death. Moreover, WE products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. Customers shall inform WE about the intent of such usage before design-in stage. In certain customer applications requiring a very high level of safety and in which the malfunction or failure of an electronic component could endanger human life or health, customers must ensure that they have all necessary expertise in the safety and regulatory ramifications of their applications. Customers acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of WE products in such safety-critical applications, notwithstanding any applicationsrelated information or support that may be provided by WE.

CUSTOMERS SHALL INDEMNIFY WE AGAINST ANY DAMAGES ARISING OUT OF THE USE OF WE PRODUCTS IN SUCH SAFETY-CRITICAL APPLICATION.

#### **USEFUL LINKS**



Application Notes www.we-online.com/appnotes



**REDEXPERT** Design Platform www.we-online.com/redexpert



Toolbox

www.we-online.com/toolbox



Product Catalogue www.we-online.com/products

#### **CONTACT INFORMATION**



appnotes@we-online.com
Tel. +49 7942 945 - 0



Würth Elektronik eiSos GmbH & Co. KG Max-Eyth-Str. 1 74638 Waldenburg Germany www.we-online.com