Dimensions: [mm]


0.5 0.5 0.0 0					Properties		Test conditions	Value	Unit	Tol.			
32 ±02 0 </th <th></th> <th></th> <th></th> <th>_</th> <th>Impedance @ 100 MHz</th> <th></th> <th></th> <th>50</th> <th>Ω</th> <th>±25%</th>				_	Impedance @ 100 MHz			50	Ω	±25%			
32±02 Image: Annual Annua			2,0	<u>− 2,0</u>	Maximum Impedance	Z _{max}	1000 MHz	82	Ω	typ.			
32:902 0.0 <					Rated Current 1	I _{R 1}	$\Delta T = 20 \text{ K}$	2000	mA	max.			
0.5 ± 0.3					Rated Current 2	I _{R 2}	$\Delta T = 40 \text{ K}$	3000	mA	max.			
0.5 ±0.3 3.2 ±0.2					DC Resistance	R _{DC}	@ 20 °C	0.025	Ω	max.			
3.2 ±0.2 Certification: 3.2 ±0.2 Image: Scale - 10:1 Image: Scale - 10:1 Image: Scale - 10:1					Туре		ŀ	ligh Current					
3.2 ±0.2 Output Completing 1001 1654 R8201 5980 (0) Scale - 101 Scale - 101 Schematic: Schematic: Schematic: Ceneral Information: Scale - 101 Scale - 101	0,5 ±0,3		WIDE BAND / HIGH SP HIGH CURRENT:										
Image: Free Conform [EDEC. JS7:086]				- /									
Scale - 10:1 Image: Scale - 10:1	<u>− 3,2 ±0,2</u>								006]				
Schematic: Image: Schematic:													
Schematic: Component Qualification AEC-0200 Grade 1 Schematic: Component Qualification AEC-0200 Grade 1 Schematic: Component Qualification Ceneral Information: Schematic: Do not use this part beyond the Rated Current as this will create excessive heat and can harm the component dispersion (in original < 40 °C; < 75 % RH				Scale - 10:1			Conforn	[IEC 61249-2-21]					
Image: Scale - 10:1 Image: Scale - 10:1 Image: Scale - 10:1 Image: Scale - 10:1 <th></th> <th></th> <td></td> <td></td> <th>Component Qualification</th> <td></td> <td>AEC</td> <td>-Q200 Grade 1</td> <td></td> <td></td>					Component Qualification		AEC	-Q200 Grade 1					
$\begin{tabular}{ c c c c c c c c c c c c c c c c c c c$		4	Schematic:	-	O								
Orget Component				General Information:									
Image: Second of the original second		~		Do not use this part beyond the Rated Current as this will create excessive heat and can harm the component									
Image: Second of the original second	ĺ Ĵ			\sim	Operating Temperature		-55	up to +125 °C					
Scale - 10:1 Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently Image: Conditions of	1,6	$\langle \rangle$				I	< 40 °C;< 75 % RH						
Scale - 10:1 With Eldentrik 600 Graft A. K.G. With Eldentrik 600 Graft A. C. K.G. With Eldentrik 600 Graft A. C. K.G. With Eldentrik 600 Graft A. S.G. With Eldentrik With					Moisture Sensitivity Level (MS		1						
Image: Sector			Test conditions of Electric					al Properties: +20 °C, 33 % RH if not specified differently					
Image: Note: Note		Scale - 10:1											
WÜRTH ELEKTRONIK NORE THAN YOU EXPECT Würth Elektronik elsos GmbH & Co. KG EMAGET Würth Elektronik elsos GmbH & Co. KG EMAGET WErCBF SMT EMI Suppression Ferrite Bead Order code 742792114								PROJECTION METHOD		⊕-			
Würth Elektronik elss GmbH & Co. KG Würth Elektronik elss GmbH & Co. KG Würth Elektronik elss GmbH & Co. KG WE-CBF SMT EMI Suppression Ferrite Bead ORDER CODE T422 945 - 0 Status WURTH ELEKTRONIK MORE THAN YOU EXPECT With Elektronic elss					DESCRIPTION		<u> </u>			Ĩ			
WÜRTH ELEKTRONIK MORE THAN YOU EXPECT EMC & Inductive Solutions 1/438 Ferrite Bead DREAD 1 Ferrite Bead 742792114			COMPLIANT COMPLIANT PREE GRADE 1		WE-CBF SMT EMI	Suppre	ession			1			
YOU EXPECT Id: +49(0)/94/2945-0 SZCITEC BUDGESUITI SINUS PRE-			WÜRTH Elektronik elSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg										
eiSos@we-online.com 1206 eiSos Valid 1/8				Tel. +49 (0) 79 42 945 - 0						1 1			
					1206		elSos	/alid		1/8			

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is not authorized for use in equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety restriction. Quipment of were leactrical cruited because severe personal injury or death, unless the parties have executed an agreement specifically governing such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in the require injury and reliability relations or performance.

Recommended Land Pattern: [mm]

Electrical Properties:

Typical Impedance Characteristics:




This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be information intended for use in equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be information intended for use in equivalent is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be information network etc.. Wurth Elektronik elSos GmbH & Co KG must be information intended to use is electronic component which is used in electrical circuits there adjust high standard is especially executed an electronic component which is used in electrical circuits there are electrical circuits ther

Derating Curve:

Packaging Specification - Tape: [mm]

Packaging Specification - Reel: [mm]



This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be informed on every electronic component which is used in effectival crustel severation (automotive control, train control, ship control), train control, ship control, train control, ship cont

Packaging Specification - Inner Carton: [mm]	Packaging Specification - Middle Carton:	[mm]
		H
Lic (mm)Wic (mm)Hic (mm)No. of Reels (pcs.)Qty. (pc.)MaterialTolerancetyp.typ. </td <td>Lmc (mm) Wmc (mm) Hmc (mm) No. of Inner Carton (pcs.) Tolerance typ. typ. typ. Value 485,00 197,00 200,00 5</td> <td>Qty. (pcs.) Material 75000 Paper</td>	Lmc (mm) Wmc (mm) Hmc (mm) No. of Inner Carton (pcs.) Tolerance typ. typ. typ. Value 485,00 197,00 200,00 5	Qty. (pcs.) Material 75000 Paper
REALS COMPLIANT COMPLEX AT COMPLE	CHECKED REVISION DATE (YYYHMM-DD) GENERAL TOLERANCE MBH 005.010 2020-10-14 DIN ISO 2768-1m DESCRIPTION WE-CBF SMT EMI Suppression	
Würth Elektronik elös GmbH & Co. KG ELEKTRONIK MORE THAN YOU EXPECT Würth 240 () 79 42 945 - 0 www.we-online.com	Ferrite Bead	2792114

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation ignal, disaster prevention, medical, public information network etc.. Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

L _C (mm) W _C (mm) H _C (mm) No. of Medium C Tolerance byp. byp.	tarton (pcs.) Qty. Material (pcs.) 150000 Paper						
		CHECKED RE	IEVISION	DATE (YYYY-MM-DD)	GENERAL TOLERANCE	000 IE7704	i1
			1	2020-10-14	GENERAL TOLERANCE DIN ISO 2768-1m	PROJECTION METHOD	
				MI Suppre	ession	ORDER CODE	
		SIZE/TYPE	-544		BUSINESS UNIT	742792114 status	PAGE
•	YOU EXPECT Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	1206			eiSos	Valid	5/8

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and reliability standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elsos GmbH & Co KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control, sing control, train control, sing control, sing control, sing control, submarine, transportation signal, disaster prevention, medical, public information network etc.. Würth Elektronik elsos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

Classification Reflow Profile for SMT components:



Classification Reflow Soldering Profile:

Profile Feature		Value
Preheat Temperature Min	T _{s min}	150 °C
Preheat Temperature Max	T _{s max}	200 °C
Preheat Time $\rm t_s$ from $\rm T_{smin}$ to $\rm T_{smax}$	t _s	60 - 120 seconds
Ramp-up Rate (T _L to T _P)		3 °C/ second max.
Liquidous Temperature	TL	217 °C
Time \mathbf{t}_{L} maintained above \mathbf{T}_{L}	tL	60 - 150 seconds
Peak package body temperature	Т _р	$T_p \leq T_c$, see Table below
Time within 5°C of actual peak temperature	t p	20 - 30 seconds
Ramp-down Rate (T _P to T _L)		6 °C/ second max.
Time 25°C to peak temperature		8 minutes max.

refer to IPC/ JEDEC J-STD-020E

Package Classification Reflow Temperature (T_c):

Properties	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
PB-Free Assembly I Package Thickness < 1.6 mm	260 °C	260 °C	260 °C
PB-Free Assembly Package Thickness 1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
PB-Free Assembly I Package Thickness > 2.5 mm	250 °C	245 °C	245 °C

refer to IPC/ JEDEC J-STD-020E

ſ				CHECKED MBH	REVISION 005.010	DATE (YYYY-MM-DD) 2020-10-14	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD		€-
		WE-CB	F SMT I	EMI Suppre	ession						
	-//5		Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany	Ferrite	Bead			ORDER CODE	792114		
		MORE THAN YOU EXPECT	einnany Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	size/type 1206			BUSINESS UNIT eiSos	status Valid		1	PAGE 6/8

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and rel

Cautions and Warnings:

The following conditions apply to all goods within the product series of WE-CBF of Würth Elektronik eiSos GmbH & Co. KG:

General:

- This electronic component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
 equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
 ship control), transportation signal, disaster prevention, medical, public information network, etc. where higher safety and reliability are
 especially required and/or if there is the possibility of direct damage or human injury.
- · Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions
 specified in the datasheet are not met, the component may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged.
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
 Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
 sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products also apply to customer specific products.

Product specific:

Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty. Wave soldering is allowed for components bigger than 0805 after evaluation and approval.
- All other soldering methods are at the customers' own risk.

Cleaning and Washing:

Washing agents used during the production to clean the customer application might damage or change the characteristics of the wire
insulation, marking or plating. Washing agents may have a negative effect on the long-term functionality of the product.

Potting:

If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the core. Expansion could damage the components. We recommend a
manual inspection after potting to avoid these effects.

Storage Conditions:

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of shipment.
- Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.

Packaging:

 The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

Handling:

- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.

ROHS COMPLIANT COMPLIANT HARDEEN 1255 C		CHECKED MBH	revision 005.010	DATE (YYYY-MM-DD) 2020-10-14	GENERAL TOLERANCE DIN ISO 2768-1m	_	PROJECTION METHOD		€-	
		WE-CBF SMT EMI Suppression					-			
-//5		Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany	Ferrite	Bead			ORDER CODE	792114		
	MORE THAN YOU EXPECT	einnany Tel. +49 (0) 79 42 945 - 0 www.we-online.com elSas@we-online.com	size/type 1206			BUSINESS UNIT eiSos	status Valid		1	PAGE 7/8

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed on every electronic component which is used in areas such as military, aerospace, aviation, nuclear control, ship control, ship control, train control, tra

Important Notes

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

			CHECKED MBH	REVISION 005.010	DATE (YYYY-MM-DD) 2020-10-14	general tolerance DIN ISO 2768-1m		PROJECTION METHOD -E	30	€-
			DESCRIPTION	F SMT I	EMI Suppre	ession				
L//5		Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany	Ferrite	Bead			ORDER CODE	792114		
	MORE THAN YOU EXPECT	einany Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	size/type 1206			BUSINESS UNIT eiSos	status Valid		- 1	PAGE 8/8

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed on every electronic component which is used in areas such as military, aerospace, aviation, nuclear control, ship control, ship control, train control, tra