
Properties **Test conditions** Value Unit Tol. Inductance 100 kHz/ 10 mA 1 ±20% L μH 9,65 2,42 4.82 **Rated Current** $\Delta T = 40 \text{ K}$ 12.5 I_{R.40K} А max. Performance Rated Current 1) $\Delta T = 40 \text{ K}$ 15.7 А max. I_{RP.40K} ±0,5 15.8 Saturation Current @ 10% $|\Delta L/L| < 10 \%$ А typ. ISAT. 10% Q Saturation Current @ 30% $|\Delta L/L| < 30 \%$ 34.2 А typ. Ω. ISAT.30% 10 DC Resistance R_{DC} @ 20 °C 8.35 mΩ max. R_{DC} 5.1 **DC Resistance** @ 20 °C mΩ typ. 1,5 ±0,5 Solder Resist 44 MHz Self Resonant Frequency f_{res} typ. 9,7 ±0,5 1) refer to IEC 62024-2-2020 No vias and traces in restricted area. 3,0 max **Certification:** 9.2 max. **RoHS Approval** Compliant [2011/65/EU&2015/863] Scale - 3:1 **REACh Approval** Conform or declared [(EC)1907/2006] Schematic: **Halogen Free** Conform [JEDEC JS709B] Halogen Free Conform [IEC 61249-2-21] **General Properties:** Ambient Temperature (referring -40 up to +85 °C to I_R) max. WE L-Code WEL-COM **Operating Temperature** -40 up to +125 °C THE COL Date Code S ω Storage Conditions (in original < 40 °C: < 75 % RH packaging) Moisture Sensitivity Level (MSL) 1 Test conditions of Performance Rated Current: refer to IEC 62024-2-2020, Class C (PCB Copper Width: 40 mm; PCB Copper Thickness: 105 µm) Temperature rise is highly dependent on many factors including PCB land pattern, trace size, and Scale - 3:1 proximity to other components. Therefore, temperature rise should be verified in application conditions. **Product Marking:** Start of Winding: Winding towards clockwise Marking 1R0 (Inductance Code) CHECKED DATE (YYYY-MM-DD) GENERAL TOLERANCE REVISION PROJECTION METHOD Marking - Date Code YYWW GЭ efa 002.002 2023-11-09 DIN ISO 2768-1m Start of Winding ٠ DESCRIPTION RoHS REACh COMPLIANT HALOGEN 125 °C **WE-LHMI SMT Power Inductor** Würth Elektronik eiSos GmbH & Co. KG ORDER CODE EMC & Inductive Solutions WURTH Max-Eyth-Str. 1 74437356010 **ELEKTRONIK** 74638 Waldenburg Germany MORE THAN Tel. +49 (0) 79 42 945 - 0 SIZE/TYPE BUSINESS UNIT STATUS PAGE YOU EXPECT www.we-online.com 8030 Valid 1/8 eiSos eiSos@we-online.com

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and rel

Recommended Land Pattern: [mm]


Electrical Properties:




This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electricial circuits that reliability and reliability functions or performance.


Typical Temperature Rise vs. Current Characteristics:

Packaging Specification - Tape and Reel: [mm]



This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik eiSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic aircuits that that quire in phase step and and reliability intronices or performance.





Packaging is referred to the international standard IEC 60286-3:2019

	L _C (mm)	W _C (mm)		No. of Inner Carton (pcs.)	Qty. (pcs.)	Material
Tolerance	typ.	typ.	typ.			
Value	252,00	348,00	354,00	4	8000	Paper

Packaging is referred to the international standard IEC 60286-3:2019

	L _{IC} (mm)	W _{IC} (mm)	H _{IC} (mm)	No. of Reel (pcs.)	Qty. (pcs.)	Material
Tolerance	typ.	typ.	typ.			
Value	336,00	336,00	44,00	2	2000	Paper

		CHECKED efa	REVISION 002.002	DATE (YYYY-MM+DD) 2023-11-09	general tolerance DIN ISO 2768-1m		PROJECTION METHOD) -	
	ROHS REACH HALOGEN 125 °C BRADE1		DESCRIPTION	MI SMT	Power Inc	luctor			
	WÜRTH WÜRTH ELECTRONIK MAR-Eyn-Skr. 1 74538 Waldenburg Germany						ORDER CODE	37356010	
	MORE THAN YOU EXPECT	Tell. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	size/type 8030			BUSINESS UNIT eiSos	status Valid		PAGE 4/8

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG mout to intended for use informed about the intent of such usage before the design-in stage. In addition, sufficient reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic advicus the require high safety and reliability and reliability

Classification Reflow Profile for SMT components:



Classification Reflow Soldering Profile:

Profile Feature		Value
Preheat Temperature Min	T _{s min}	150 °C
Preheat Temperature Max	T _{s max}	200 °C
Preheat Time $\rm t_s$ from $\rm T_{smin}$ to $\rm T_{smax}$	t _s	60 - 120 seconds
Ramp-up Rate (T _L to T _P)		3 °C/ second max.
Liquidous Temperature	TL	217 °C
Time t_L maintained above T_L	tL	60 - 150 seconds
Peak package body temperature	Т _р	$T_p \leq T_c$, see Table below
Time within 5°C of actual peak temperature	t p	20 - 30 seconds
Ramp-down Rate (T _P to T _L)		6 °C/ second max.
Time 25°C to peak temperature		8 minutes max.

refer to IPC/ JEDEC J-STD-020E

Package Classification Reflow Temperature (T_c):

Properties	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
PB-Free Assembly I Package Thickness < 1.6 mm	260 °C	260 °C	260 °C
PB-Free Assembly Package Thickness 1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
PB-Free Assembly I Package Thickness > 2.5 mm	250 °C	245 °C	245 °C

refer to IPC/ JEDEC J-STD-020E

		CHECKED efa	REVISION 002.002	DATE (YYYY-MM+DD) 2023-11-09	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD	
		WE-LHMI SMT Power Inductor						
Würth Elektronik elSos GrmbH & Co. KG EMC & Inductive Solutions Max-Egth-Str. 1 74638 Waldenburg Germany						ORDER CODE	37356010	
MORE THAN YOU EXPECT	Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	size/type 8030			BUSINESS UNIT eiSos	status Valid		page 5/8

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and rel

Furth	er information	REDEXPERT:
Comp	onent Libraries:	Calculate losses for 74
	Altium_WE-LHMI (23a)	
@ P S	Downloads_CADENCE_WE-LHMI (23a)	
@P 3	Download_CadStar_WE-LHMI (19a)	
Exc	Eagle_WE-LHMI (23a)	
231	Download_IGS_WE-LHMI-8030	
FEF	PSpice_WE-LHMI (23a)	
ar	Download_STP_WE-LHMI-8030	
800	Spectre_WE-LHMI (23a)	
Free S	ample Order:	
Order fre	e samples of this article directly here!	
Tutori	als: e Coil Inductors (PDF)	

CHECKED REVISION DATE (YYYY-MM-DD) GENERAL TOLERANCE PROJECTION METHOD \oplus GÐ efa 002.002 2023-11-09 DIN ISO 2768-1m DESCRIPTION RoHS COMPLIANT REACh HALOGEN 125 °C GRADE 1 **WE-LHMI SMT Power Inductor** Würth Elektronik eiSos GmbH & Co. KG ORDER CODE EMC & Inductive Solutions WÜRTH ELEKTRONIK MORE THAN YOU EXPECT Max-Eyth-Str. 1 74437356010 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com SIZE/TYPE STATUS BUSINESS UNIT PAGE 6/8 8030 eiSos Valid

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic advicus the runterioa circuits that must control such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic advicus that must and require high safety and reliability an

Calculate losses for 74437356010 in REDEXPERT

Cautions and Warnings:

The following conditions apply to all goods within the product series of WE-LHMI of Würth Elektronik eiSos GmbH & Co. KG:

General:

- This electronic component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
 equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
 ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are
 especially required and/or if there is the possibility of direct damage or human injury.
- · Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions
 specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged.
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
 Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
 sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products also apply to customer specific products.

Product specific:

Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- All other soldering methods are at the customers' own risk
- Strong forces which may affect the coplanarity of the components' electrical connection with the PCB (i.e. pins), can damage the part, resulting in avoid of the warranty.

Cleaning and Washing:

- Washing agents used during the production to clean the customer application might damage or change the characteristics of the wire
 insulation, marking or plating. Washing agents may have a negative effect on the long-term functionality of the product.
- Using a brush during the cleaning process may break the wire due to its small diameter. Therefore, we do not recommend using a brush during the PCB cleaning process.

Potting:

If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the core. Expansion could damage the component. We recommend a
manual inspection after potting to avoid these effects.

Storage Conditions:

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of shipment.
- Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.

Packaging:

 The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

Handling:

- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- Applying currents with audio-frequency signals may result in audible noise due to the magnetostrictive material properties.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.

		CHECKED	REVISION 002.002	DATE (YYYY-MM-DD) 2023-11-09	general tolerance DIN ISO 2768-1m		PROJECTION METHOD	$- \bigcirc ($	€-	
	ROHS REACH HALOGEN 125 °C COMPLIANT COMPLIANT FREE GRADE		DESCRIPTION	WE-LHMI SMT Power Inductor						
		EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg					ORDER CODE	373560	10	
	MORE TH YOU EXP	AN Tel. +49 (0) 79 42 945 - 0	size/type 8030			BUSINESS UNIT eiSos	status Valid		1	page 7/8

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intern of such usage before the design-in stage. In addition, sufficient reliability evaluation, transportation, signal, disaster prevention, medical, public information network etc... Würth Elektronik elSos GmbH & Co KG must be informed about the intern of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electricia circuits that and reliability functions or performance.

Important Notes

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

COMPANY ROMAN		CHECKED efa	REVISION 002.002	DATE (YYYY-MM-DD) 2023-11-09	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD	-
				Power Inc				
WÜRTH WÜRTH Kara Kara Kara Kara Kara Kara Kara Kar				rowerind		order code	37356010	
MORE THAN YOU EXPECT	Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com elSos@we-online.com	size/type 8030			BUSINESS UNIT eiSos	status Valid		PAGE 8/8

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic circuits that require high asteging and reliability functions or performance.