




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



**ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:**

D.C. RESISTANCE (@20°C):	9-8 , 0.065 Ohms ±10%.
	7-6 , 0.065 Ohms ±10%.
	2-4 , 0.700 Ohms ±10%.
DIELECTRIC RATING:	4500VAC, 1 minute tested by applying 4500VAC for 1 second between pins 9-2(9+7).
	500VAC, 1 minute tested by applying 625VAC for 1 second between pins 9-7.
INDUCTANCE:	15.00µH ±10%, 250kHz, 100mVAC, 0mADC, 9-8, Ls.
LEAKAGE INDUCTANCE:	1.0µH max., 100kHz, 100mVAC, 9-8(7+6,2+4), Ls.
URNS RATIO:	( 2-4 ):( 9-8 ) , ( 3.250 ):(1.00) , ±1%.
	( 2-4 ):( 7-6 ) , ( 3.250 ):(1.00) , ±1%.

Designed to comply with the following requirements as defined by IEC61558-2-17:

- Reinforced insulation for a primary circuit at a working voltage of 400VDC.

OPERATING TEMPERATURE RANGE: -40°C to 125°C including temp. rise.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

<b>WE-Midcom, Inc.</b> Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: ±1°      Fractions: ±1/64 Decimals: ±.005 (.127mm)		<b>WE-Midcom, Inc.</b>	
	Drawing Title <h1>Transformer</h1>		Drawing Number <h2>750312666</h2>	Rev. 00
Revisions: See Sheet 1		Scale ----	Sheet 2 of 5	
This drawing is dual dimensioned. Dimensions in brackets are in millimeters		Engineer:TST	10/04/2011	