


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	0.200 ohms max.
INDUCTANCE	1-3 100kHz, 100mVAC, Ls	154 - 172uH
INDUCTANCE	1-3 100kHz, 100mVAC, 7.8ADC, Ls	150uH min.
SELF RESONANCE	1-3 -	1.5MHz typ.
DIELECTRIC	1-Core 625VAC, 2 seconds	500VAC, 1 minute




TERM. NO.'s FOR REFERENCE ONLY

LOT CODE & DATE CODE

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +85°C.



RECOMMENDED P.C. PATTERN, COMPONENT SIDE

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-1100 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE <b>INDUCTOR</b>	PART NO. <b>750317797</b>
6B	1/19			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750317797	SPECIFICATION SHEET 1 OF 1
6A	9/18	SEE REVISION SHEET FOR REVISION LEVEL				