




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-4 @20°C	0.16 ohms max.
D.C. RESISTANCE	1-2 @20°C	0.11 ohms max.
INDUCTANCE	3-4 10kHz, 1V, Ls	300.00µH ±10%
URNS RATIO	(4-3):(1-2)	10.33:1, ±2%



RECOMMENDED P.C. PATTERN, COMPONENT SIDE

Tooling Required

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

REFERENCE DESIGN

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	Packaging Specifications	<p>CONVENTION PLACEMENT</p>	<p>Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]</p>	<p>DRAWING TITLE</p> <p>INDUCTOR</p>	<p>PART NO.</p> <p>750343888</p>
DATE	Method: Tray PKG-TBD				
ENG	IYU				
REV.	01				
DATE	12/6/2018	www.we-online.com/midcom			