




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect




TERM. NO.'s FOR REF. ONLY



Customer to tie terminals 1+2 and 3+4 internally on PCB.

6B



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-4 tie(1+2, 3+4), @20°C	0.015 ohms max.
D.C. RESISTANCE	5-8 @20°C	11.72 ohms ±10%
INDUCTANCE	1-4 tie(1+2, 3+4), 10kHz, 100mVAC, Ls	4.00uH ±10%
SATURATION CURRENT	20% rolloff from initial	6.5A
LEAKAGE INDUCTANCE	1-4 tie(1+2, 3+4, 5+8), 100kHz, 10mVAC, Ls	100nH typ., 200nH max.
DIELECTRIC	1-8 tie(3+4), 625VAC, 1 second	500VAC, 1 minute
TURNS RATIO	(5-8):(4-1), tie(1+2, 3+4)	24:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed for functional insulation.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0328 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750314020
6B	9/14			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750314020	
6A	8/14	SEE REVISION SHEET FOR REVISION LEVEL				SPECIFICATION SHEET 1 OF 1