




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-2 @20°C	0.795 ohms ±10%
D.C. RESISTANCE	5-4 @20°C	0.019 ohms ±30%
D.C. RESISTANCE	7-6 @20°C	0.021 ohms ±30%
D.C. RESISTANCE	8-9 @20°C	0.160 ohms ±10%
D.C. RESISTANCE	10-11 @20°C	0.165 ohms ±10%
D.C. RESISTANCE	13-14 @20°C	0.175 ohms ±10%
INDUCTANCE	3-2 10kHz, 100mV, Ls	2.50mH ±15%
SATURATION CURRENT	20% rolloff from initial	200mA
LEAKAGE INDUCTANCE	3-2 tie(4+5+6+7, 8+9+10+11+13+14), 100kHz, 100mV, Ls	8.7µH typ., 17.4µH max.
DIELECTRIC	2-14 tie(3+4, 7+8+11+13), 2000VAC, 1 second	2000VAC, 1 minute
DIELECTRIC	2-5 2000VAC, 1 second	
DIELECTRIC	6-14 tie(7+8, 11+13), 2000VAC, 1 second	
DIELECTRIC	6-8 tie(7+14, 9+10), 2000VAC, 1 second	
TURNS RATIO	(3-2):(5-4)	8:1, ±1%
TURNS RATIO	(3-2):(7-6)	14:1, ±1%
TURNS RATIO	(3-2):(8-9)	11.2:1, ±1%
TURNS RATIO	(3-2):(10-11)	11.2:1, ±1%
TURNS RATIO	(3-2):(13-14)	11.2:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Safety standard undefined

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	Packaging Specifications	<p>CONVENTION PLACEMENT</p>	<p>Tolerances unless otherwise specified:</p> <p>Angles: ±1° Decimals: ±.005 [.13]</p> <p>Fractions: ±1/64 Footprint: ± .001 [.03]</p>	DRAWING TITLE	PART NO.
DATE	Method: Tray				
ENG	KLM	PKG-0737			
REV.	02				
DATE	10/18/2019	www.we-online.com/midcom			SPECIFICATION SHEET 1 OF 1