




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-4 tie(2+3, 4+5), @20°C	0.112 ohms ±10%
INDUCTANCE	2-4 tie(2+3, 4+5), 10kHz, 100mV, Ls	500.00µH ±10%
SATURATION CURRENT	2-4 tie(2+3, 4+5), 20% rolloff from initial	13.5A TBD



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Application of the transformer allows for the leadwires between terminals 2&3 and 4&5 to solder bridge.

Customer to tie terminals 2+3 and 4+5 on PC board.

Preliminary

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	SP	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]	DRAWING TITLE INDUCTOR	PART NO.
DATE	4/1/2020	Method: Tray PKG-0986		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		750319122
ENG	PLP					
REV.	00					
DATE	4/17/2020	www.we-online.com/midcom				SPECIFICATION SHEET 1 OF 1