



Product / Process Change Notification (PCN)

- Major Change
 Minor Change

PCN Number: PCN_WPME-FDSM_173951275_20250120

Affected Series: WPME-FDSM

Affected Part Number: 173951275

PCN Date: 2024-12-20 (YYYY-MM-DD)

Effective Date: 2025-01-20 (YYYY-MM-DD)

Change Category:

- Equipment/Location
 General Data
 Material
 Process
 Product Design
 Shipping/Packaging
 Supplier
 Software

Contact: Product Management

Phone: +49 (0) 7942 - 945 5001

Fax: +49 (0) 7942 - 945 5179

E-Mail: pcn.eisos@we-online.com

Datasheet Change:

- Yes No

Attachment:

- Yes No

DESCRIPTION OF CHANGE:

Due to an improvement of the production capability, Würth Elektronik eiSos has shifted the production of the affected part number to a new factory location.

With the aim of an extended product applicability, Würth Elektronik eiSos has updated the BOM used in the module to ensure the best performance and the electrical specifications.

There will be no change in fit or quality of the product.

The new revision of the affected part number will be sent out after the previous revision is out of stock (according to FIFO - first-in, first-out).

DETAILS OF CHANGE:

All changes indicated below apply to the part number in this PCN.

Previous production line	New production line
Lot number beginning with: 489xxxxxxxxxxx	Lot number beginning with: 676xxxxxxxxxxx
Country of origin: China	Country of origin: China



The part numbers of the FDSM series are now distributed in single datasheets instead of the previous family datasheet approach

Before Change

17395xx75
Magi³C Power Module
 WPME-FDSM - Fixed Step Down Regulator Module

Maximum Input 74.5V / 0.5A / Fixed Output 3.3V, 5V or 12V

DESCRIPTION

The FDSM series of the Magi³C Power Module family is a fixed output voltage, fully integrated DC-DC power supply including the controller IC, inductor and capacitors all in one package.

For optimal performance the module is recommended for use with an external input capacitor, reducing design effort and complexity to a minimum.

The FDSM ensures fast time to market and low development costs.

The module is specially suited for high transient 48V bus applications such as industrial motor drive control systems.

48V to 3.3V conversion achieves up to 89%. 48V to 5V conversion achieves up to 93%. 48V to 12V conversion achieves up to 95% efficiency.

The standard THT (11.5 x 9 x 17.5mm) package allows for easy assembly.

TYPICAL APPLICATIONS

FEATURES

- Peak efficiency up to 95%
- Current capability up to 0.5A
- Input voltage up to 74.5V
- Minimum input voltage / output voltage:
 - 9V / 3.3V (173950375)
 - 9V / 5V (17395075)
 - 18V / 12V (173951275)
- No minimum load required
- Partially integrated input and output capacitors
- Integrated inductor
- Low output voltage ripple (<50mV_{pp})
- Current mode control
- Internal soft-start
- Thermal shutdown
- Short circuit protection
- Cycle by cycle current limit
- Pin compatible with the FDSM power modules series
- Ambient temperature range: -40°C to 85°C
- RoHS & REACH compliant
- Case and potting material UL 94 (flammability testing) certified
- Complies with EN55032 (CISPR-32) class B conducted and radiated emissions standard

After Change

173951275
Magi³C Power Module
 WPME-FDSM - Fixed Step Down Regulator Module

Maximum input 74.5V / 0.5A / Fixed Output 12V

DESCRIPTION

The FDSM series of the Magi³C Power Module family is a fixed output voltage, fully integrated DC-DC power supply including the controller IC, inductor and capacitors all in one package.

For optimal performance the module is recommended for use with an external input capacitor, reducing design effort and complexity to a minimum.

The FDSM ensures fast time to market and low development costs.

The module is specially suited for high transient 48V bus applications such as industrial motor drive control systems.

The 173951275 module achieves an efficiency up to 90%.

The standard THT (11.5 x 8.5 x 17.5mm) package allows for easy assembly.

FEATURES

- Peak efficiency up to 90%
- Current capability up to 0.5A
- Input voltage up to 74.5V
- No minimum load required
- Partially integrated input and output capacitors
- Integrated inductor
- Low output voltage ripple (<50mV_{pp})
- PFM/PWM mode
- Internal soft-start
- Thermal shutdown
- Short circuit protection
- Cycle by cycle current limit
- Pin compatible with the FDSM power modules series
- Ambient temperature range: -40°C to 85°C
- RoHS & REACH compliant
- Complies with EN55032 (CISPR-32) class B conducted and radiated emissions standard

The datasheet electrical specifications (maximum / electrical) have been adjusted based on the new design.

Before Change

5 ABSOLUTE MAXIMUM RATINGS

Caution:
 Exceeding the listed absolute maximum ratings may affect the device negatively and may cause permanent damage.

Table 3: Absolute maximum ratings.

SYMBOL	PARAMETER	LIMIT		UNIT
		MIN ⁽¹⁾	MAX ⁽¹⁾	
V _{IN}	Input pin voltage 17395xx75	-0.3	90	V
V _{OUT}	Output pin voltage 3.3Vout / 5Vout version	-0.3	16	V
	Output pin voltage 12Vout version	-0.3	25	V
T _{storage}	Assembled, non-operating storage temperature	-40	125	°C
V _{esd}	ESD Voltage (Human Body Model), according to EN61000-4-2 ⁽²⁾	-4	4	kV

After Change

5 ABSOLUTE MAXIMUM RATINGS

Caution:
 Exceeding the listed absolute maximum ratings may affect the device negatively and may cause permanent damage.

Table 5: Absolute maximum ratings.

SYMBOL	PARAMETER	LIMIT		UNIT
		MIN ⁽¹⁾	MAX ⁽¹⁾	
V _{IN}	Input pin voltage	-0.3	100	V
V _{OUT}	Output pin voltage	-0.3	16	V
T _{storage}	Assembled, non-operating storage temperature	-40	125	°C
V _{esd}	ESD Voltage (Human Body Model), according to EN61000-4-2 ⁽²⁾	-4	4	kV



7 ELECTRICAL SPECIFICATIONS						
Caution: MIN and MAX limits are valid for the recommended ambient temperature range of -40°C to 85°C. Typical values represent statistically the utmost probable values at the following conditions: $V_{IN}=48V$ (173950375, 173950575 and 173951275), $I_{OUT}=0.5A$, $T_A=25^{\circ}C$, unless otherwise noted.						
Table 5: Electrical specifications.						
SYMBOL	PARAMETER	TEST CONDITIONS	LIMIT			UNIT
			MIN ⁽¹⁾	TYP ⁽²⁾	MAX ⁽¹⁾	
Output Current						
I_{CL}	Current limit threshold	$V_{OUT}=3.3$	-	1.1	-	A
		$V_{OUT}=5$	-	1.2	-	A
		$V_{OUT}=12$	-	0.9	-	A
Output Voltage						
V_{OUT}	Regulated output voltage	173950375	-	3.3	-	V
		173950575	-	5	-	V
		173951275	-	12	-	V
		Line regulation	$I_{OUT}=0.5A$	-0.4	±0.2	0.4
	Load Regulation	10% to 100% load	-0.6	±0.4	0.6	%
		$V_{OUT}=3.3V$, $I_{OUT}=0.5A$	-4.5	±3.5	4.5	%
	Total output voltage regulation	$V_{OUT}=5V/12V$, $I_{OUT}=0.5A$	-3	±2	3	%
		External 2x $C_{OUT}=10\mu F$, 25V, X5R, 20MHz BWL ⁽³⁾	-	-	-	-
	Output voltage ripple	3.3V, 0.5A	-	40	-	mV _{pp}
		5V / 12V, 0.5A	-	30	-	mV _{pp}
Switching Frequency						
f_{SW}	Switching frequency	$V_{OUT}=3.3V$, $I_{OUT}=0.5A$	-	166	-	kHz
		$V_{OUT}=5V$, $I_{OUT}=0.5A$	-	250	-	kHz
		$V_{OUT}=12V$, $I_{OUT}=0.5A$	-	400	-	kHz
Input Current						
I_{IN}	No load input current	Operating, switching	-	0.3	1	mA
Efficiency						
η	Efficiency, $I_{OUT}=0.5A$	$V_{IN}=9V$, $V_{OUT}=3.3V$	-	89	-	%
		$V_{IN}=48V$, $V_{OUT}=3.3V$	-	81	-	%
		$V_{IN}=9V$, $V_{OUT}=5V$	-	92	-	%
		$V_{IN}=48V$, $V_{OUT}=5V$	-	86	-	%
		$V_{IN}=18V$, $V_{OUT}=12V$	-	95	-	%
		$V_{IN}=48V$, $V_{OUT}=12V$	-	91	-	%

7 ELECTRICAL SPECIFICATIONS
Caution:
 MIN and MAX limits are valid for the recommended ambient temperature range of -40°C to 85°C. Typical values represent statistically the utmost probable values at the following conditions: $V_{IN}=48V$, $V_{OUT}=12V$, $I_{OUT}=0.5A$, $T_A=25^{\circ}C$, unless otherwise noted.

7 ELECTRICAL SPECIFICATIONS						
Table 7: Electrical specifications.						
SYMBOL	PARAMETER	TEST CONDITIONS	LIMIT			UNIT
			MIN ⁽¹⁾	TYP ⁽²⁾	MAX ⁽¹⁾	
Output Current						
I_{CL}	Current limit threshold		-	1.2	-	A
Output Voltage						
V_{OUT}	Regulated output voltage		-	12	-	V
	Line Regulation		-	2.5	-	%
	Load Regulation	10% to 100% load	-	2.0	-	%
	Total output voltage regulation		-	3	-	%
	Output voltage ripple		-	75	-	mV _{pp}
Switching Frequency						
f_{SW}	Switching frequency		-	350	-	kHz
Input Current						
I_{IN}	No load input current	Operating, switching	-	0.2	-	mA
Efficiency						
η	Efficiency		-	90	-	%

The datasheet package specifications have been adjusted based on the new design.

Before Change	After Change																																								
<p>10 PACKAGE SPECIFICATIONS</p> <p>Table 8: Package specifications.</p> <table border="1"> <thead> <tr> <th>ITEM</th> <th>PARAMETER</th> <th>TYP⁽¹⁾</th> <th>UNIT</th> </tr> </thead> <tbody> <tr> <td>Case</td> <td>Black flame-retardant and heat-resistant plastic (UL94 V-0)</td> <td>-</td> <td>-</td> </tr> <tr> <td>Potting material</td> <td>Silicone, UL94V-0</td> <td>-</td> <td>-</td> </tr> <tr> <td>Weight</td> <td></td> <td>3.8</td> <td>g</td> </tr> <tr> <td>Vibration</td> <td>5g for 20 min</td> <td>MIL-STD-202, Method 204</td> <td></td> </tr> </tbody> </table>	ITEM	PARAMETER	TYP ⁽¹⁾	UNIT	Case	Black flame-retardant and heat-resistant plastic (UL94 V-0)	-	-	Potting material	Silicone, UL94V-0	-	-	Weight		3.8	g	Vibration	5g for 20 min	MIL-STD-202, Method 204		<p>10 PACKAGE SPECIFICATIONS</p> <p>Table 10: Package specifications.</p> <table border="1"> <thead> <tr> <th>ITEM</th> <th>PARAMETER</th> <th>TYP⁽¹⁾</th> <th>UNIT</th> </tr> </thead> <tbody> <tr> <td>Case</td> <td>Black flame-retardant and heat-resistant plastic (UL94 V-0)</td> <td>-</td> <td>-</td> </tr> <tr> <td>Potting material</td> <td>Silicone, UL94V-0</td> <td>-</td> <td>-</td> </tr> <tr> <td>Weight</td> <td></td> <td>4</td> <td>g</td> </tr> <tr> <td>Vibration</td> <td>5g for 20 min</td> <td>MIL-STD-202, Method 204</td> <td></td> </tr> </tbody> </table>	ITEM	PARAMETER	TYP ⁽¹⁾	UNIT	Case	Black flame-retardant and heat-resistant plastic (UL94 V-0)	-	-	Potting material	Silicone, UL94V-0	-	-	Weight		4	g	Vibration	5g for 20 min	MIL-STD-202, Method 204	
ITEM	PARAMETER	TYP ⁽¹⁾	UNIT																																						
Case	Black flame-retardant and heat-resistant plastic (UL94 V-0)	-	-																																						
Potting material	Silicone, UL94V-0	-	-																																						
Weight		3.8	g																																						
Vibration	5g for 20 min	MIL-STD-202, Method 204																																							
ITEM	PARAMETER	TYP ⁽¹⁾	UNIT																																						
Case	Black flame-retardant and heat-resistant plastic (UL94 V-0)	-	-																																						
Potting material	Silicone, UL94V-0	-	-																																						
Weight		4	g																																						
Vibration	5g for 20 min	MIL-STD-202, Method 204																																							

The datasheet MTBF specifications have been adjusted based on the new design.

Before Change	After Change																							
<p>9 RELIABILITY</p> <p>Table 7: Reliability.</p> <table border="1"> <thead> <tr> <th>SYMBOL</th> <th>PARAMETER</th> <th>TEST CONDITIONS</th> <th>TYP⁽¹⁾</th> <th>UNIT</th> </tr> </thead> <tbody> <tr> <td>MTBF</td> <td>Mean time between failures</td> <td>MIL-HDBK-217F, 25°C</td> <td>5000 · 10³</td> <td>h</td> </tr> </tbody> </table>	SYMBOL	PARAMETER	TEST CONDITIONS	TYP ⁽¹⁾	UNIT	MTBF	Mean time between failures	MIL-HDBK-217F, 25°C	5000 · 10 ³	h	<p>9 RELIABILITY</p> <p>Table 9: Reliability.</p> <table border="1"> <thead> <tr> <th>SYMBOL</th> <th>PARAMETER</th> <th>TEST CONDITIONS</th> <th>TYP⁽¹⁾</th> <th>UNIT</th> </tr> </thead> <tbody> <tr> <td rowspan="2">MTBF⁽²⁾</td> <td rowspan="2">Mean Time Between Failures</td> <td>MIL-HDBK-217F, 25°C</td> <td>6849 · 10³</td> <td>h</td> </tr> <tr> <td>MIL-HDBK-217F, 85°C</td> <td>1337 · 10³</td> <td>h</td> </tr> </tbody> </table>	SYMBOL	PARAMETER	TEST CONDITIONS	TYP ⁽¹⁾	UNIT	MTBF ⁽²⁾	Mean Time Between Failures	MIL-HDBK-217F, 25°C	6849 · 10 ³	h	MIL-HDBK-217F, 85°C	1337 · 10 ³	h
SYMBOL	PARAMETER	TEST CONDITIONS	TYP ⁽¹⁾	UNIT																				
MTBF	Mean time between failures	MIL-HDBK-217F, 25°C	5000 · 10 ³	h																				
SYMBOL	PARAMETER	TEST CONDITIONS	TYP ⁽¹⁾	UNIT																				
MTBF ⁽²⁾	Mean Time Between Failures	MIL-HDBK-217F, 25°C	6849 · 10 ³	h																				
		MIL-HDBK-217F, 85°C	1337 · 10 ³	h																				

The diagrams shown in chapter TYPICAL PERFORMANCE CURVES are updated based on new electrical specifications. The used test conditions stay the same as before.


Due to the change of IC and change the internal BOM is changed. The changes in component values and new internal reference voltage are indicated in the BLOCK DIAGRAM chapter.

Before Change	After Change
<p>13 BLOCK DIAGRAM</p> <p>Figure 16: 17395xx75 block diagram.</p> <p>14 CIRCUIT DESCRIPTION</p> <p>The Mag¹C power modules 17395xx75 are all synchronous step-down regulator with integrated IC, power inductor, input and output capacitors. The control scheme is based on a constant on-time (COT) regulation loop.</p> <p>The V_{OUT} of the regulator is divided by the internal feedback resistor network and fed into the error amplifier, which compares this signal with the internal 1.2V reference. The error amplifier controls the on-time of a fixed frequency pulse width generator, which drives the MOSFET.</p> <p>To achieve a regulated output voltage the off-time is modulated. It is stable with low ESR output capacitors. No external compensation network is required. This architecture supports fast transient response and very small output voltage ripple values ($<50mV_p$) are achieved.</p>	<p>13 BLOCK DIAGRAM</p> <p>Figure 8: Block diagram.</p> <p>14 CIRCUIT DESCRIPTION</p> <p>The Mag¹C power module 173951275 is based on a synchronous step-down regulator with integrated IC, power inductor, input and output capacitors. The control scheme is based on a constant on-time (COT) regulation loop.</p> <p>The V_{OUT} of the regulator is divided by the internal feedback resistor network and fed into the error amplifier, which compares this signal with the internal 1.225V reference. The error amplifier controls the on-time of a fixed frequency pulse width generator, which drives the MOSFET.</p> <p>To achieve a regulated output voltage the off-time is modulated. It is stable with low ESR output capacitors. No external compensation network is required. This architecture supports fast transient response and very small output voltage ripple values ($<50mV_p$) are achieved.</p>


The handling recommendations for the wave solder profile have been expanded to include the maximum allowable time for each wave.

Before Change	After Change																																										
<p>18.1 Solder Profile</p> <p>Table 10: Wave solder profile.</p> <table border="1"> <thead> <tr> <th>Profile Feature</th> <th>Old standard (Pb)</th> <th>New (Pb-free)</th> </tr> </thead> <tbody> <tr> <td>Time within peak temperature t_p</td> <td>10s</td> <td>10s</td> </tr> <tr> <td>Average ramp-up rate between T_s and T_p</td> <td>200°C/s</td> <td>200°C/s</td> </tr> <tr> <td>Final preheat temperature T_s</td> <td>130°C/s</td> <td>130°C/s</td> </tr> <tr> <td>Peak temperature T_p</td> <td>+235°C/s</td> <td>+260°C/s</td> </tr> <tr> <td>Ramp-down rate</td> <td>-5°C/s</td> <td>-5°C/s</td> </tr> <tr> <td>Heating rate during preheat</td> <td>4°C/s</td> <td>4°C/s</td> </tr> </tbody> </table>	Profile Feature	Old standard (Pb)	New (Pb-free)	Time within peak temperature t_p	10s	10s	Average ramp-up rate between T_s and T_p	200°C/s	200°C/s	Final preheat temperature T_s	130°C/s	130°C/s	Peak temperature T_p	+235°C/s	+260°C/s	Ramp-down rate	-5°C/s	-5°C/s	Heating rate during preheat	4°C/s	4°C/s	<p>19.1 Soldering Profile</p> <p>Table 12: Wave solder profile.</p> <table border="1"> <thead> <tr> <th>Profile Feature</th> <th>Old standard (Pb)</th> <th>New (Pb-free)</th> </tr> </thead> <tbody> <tr> <td>Time within peak temperature t_p</td> <td>max. 10s max. 5s each wave</td> <td>max. 10s max. 5s each wave</td> </tr> <tr> <td>Average ramp-up rate</td> <td>200°C/s</td> <td>200°C/s</td> </tr> <tr> <td>Final preheat temperature T_s</td> <td>130°C/s</td> <td>130°C/s</td> </tr> <tr> <td>Peak temperature T_p</td> <td>+235°C/s</td> <td>+260°C/s</td> </tr> <tr> <td>Ramp-down rate</td> <td>-5°C/s</td> <td>-5°C/s</td> </tr> <tr> <td>Heating rate during preheat</td> <td>4°C/s</td> <td>4°C/s</td> </tr> </tbody> </table>	Profile Feature	Old standard (Pb)	New (Pb-free)	Time within peak temperature t_p	max. 10s max. 5s each wave	max. 10s max. 5s each wave	Average ramp-up rate	200°C/s	200°C/s	Final preheat temperature T_s	130°C/s	130°C/s	Peak temperature T_p	+235°C/s	+260°C/s	Ramp-down rate	-5°C/s	-5°C/s	Heating rate during preheat	4°C/s	4°C/s
Profile Feature	Old standard (Pb)	New (Pb-free)																																									
Time within peak temperature t_p	10s	10s																																									
Average ramp-up rate between T_s and T_p	200°C/s	200°C/s																																									
Final preheat temperature T_s	130°C/s	130°C/s																																									
Peak temperature T_p	+235°C/s	+260°C/s																																									
Ramp-down rate	-5°C/s	-5°C/s																																									
Heating rate during preheat	4°C/s	4°C/s																																									
Profile Feature	Old standard (Pb)	New (Pb-free)																																									
Time within peak temperature t_p	max. 10s max. 5s each wave	max. 10s max. 5s each wave																																									
Average ramp-up rate	200°C/s	200°C/s																																									
Final preheat temperature T_s	130°C/s	130°C/s																																									
Peak temperature T_p	+235°C/s	+260°C/s																																									
Ramp-down rate	-5°C/s	-5°C/s																																									
Heating rate during preheat	4°C/s	4°C/s																																									

The mechanical dimensions have been updated based on new production. The SIP-3 package shape stays the same but with slightly deviated package width and adjusted tolerances.



The tube specifications have been adjusted.





RELIABILITY / QUALIFICATION OF CHANGE:

An additional reliability testing was performed and approved.

Additional details of the tests can be found in the table below:

Test Item	Sample Size	Reference	Test Conditions	Acceptance
Temperature Cycling	25	JESD22 Method JA-104	Temperature: -40°C to 85°C Testing Time: 500 cycles Test Cycles/h: 3 Min. soak time: 1 min	Approved
High Temperature Operational Life	78	JESD22-A108	Tj: 125°C Testing Time: 1000h	Approved
Electrical Characterization	30	User Spec.	measure electrical DC performance @25 °C, - 40 °C, 105 °C Transient performance tests @25°C Thermal derating measurement.	Approved
Low Temperature Storage Life	25	JESD22-A119	500hrs @ -55°C	Approved
High Temperature Storage Life	25	JESD22-A119	500hrs @ 125°C	Approved
Steady State Humidity	25	MIL-STD-202, Method 106	Temperature: 65± 2°C Testing Time: 504h Humidity: 95%RH	Approved
Mechanical Shock	30	MIL-STD-202-213	3 shocks in each direction (x, -x, y, -y, z, -z), peak value of 100 g, duration 6 ms, half-sine, velocity change 12.3 ft/s.	Approved
Vibration	30	MIL-STD-202-204	5 g for 20 min, 12 cycles each of 3 orientations. Test from 10 Hz to 2000 Hz.	Approved