



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-5 @20°C	0.230 ohms max.
D.C. RESISTANCE	6-8 @20°C	50.000 ohms max.
D.C. RESISTANCE	8-10 @20°C	40.000 ohms max.
INDUCTANCE	1-3 100kHz, 100mVAC, Ls	30.00uH min.
LEAKAGE INDUCTANCE	1-5 tie(6+8+10), 100kHz, 100mVAC, Ls	400nH max.
DIELECTRIC	1-10 1250VAC, 1 second	1000VAC, 1 minute
TURNS RATIO	(8-6):(1-5)	19.5:1, ±1%
TURNS RATIO	(10-8):(1-5)	19.5:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Functional insulation only.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0654 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750343584
6A	3/18	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750343584	SPECIFICATION SHEET 1 OF 1