



<b>Product/Process Change Notice (PCN)</b>	
<input checked="" type="checkbox"/> Major Change <input type="checkbox"/> Minor Change	
<b>PCN Number:</b> PCN_UtSTST_20250319  <b>Affected Series:</b> WE-STST  <b>Affected Part Number:</b> 74930000, 74930100  <b>PCN Date:</b> 2024-12-19 (YYYY-MM-DD) <b>Effective Date:</b> 2025-03-19 (YYYY-MM-DD)	<b>Change Category:</b> <input type="checkbox"/> Equipment/Location <input type="checkbox"/> General Data <input type="checkbox"/> Material <input type="checkbox"/> Process <input checked="" type="checkbox"/> Product Design <input type="checkbox"/> Shipping/Packaging <input type="checkbox"/> Supplier <input type="checkbox"/> Software
<b>Contact:</b> Product Management <b>Phone:</b> +49 (0) 7942 - 945 5001 <b>Fax:</b> +49 (0) 7942 - 945 5179 <b>E-Mail:</b> pcn.eisos@we-online.com	<b>Datasheet Change:</b> <input type="checkbox"/> Yes <input checked="" type="checkbox"/> No  <b>Attachment:</b> <input type="checkbox"/> Yes <input checked="" type="checkbox"/> No
<b>DESCRIPTION OF CHANGE:</b> To improve the processability, Würth Elektronik eiSos will change the core sizes of these products.  There will be no change in fit, function, quality or reliability of the product.  The new revision of the affected order codes will be sent out after the previous revision is out of stock (according to FIFO - first-in, first-out).	
<b>DETAILS OF CHANGE:</b> <ul style="list-style-type: none"> <li><b>Core dimensions:</b> change core height of top core from 1.20 mm to 0.85 mm, and bottom core from 1.60 mm to 1.90 mm.</li> </ul>	
<b>Before Change</b>	<b>After Change</b>
	



**RELIABILITY / QUALIFICATION OF CHANGE:**

Product approval is according to the specification criteria and is internally released by the Product Management Department. The following items are part of the internal release process:

Test Item	Sample Size	Reference	Test Conditions	Acceptance
Visual Appearance	200	Product specification	Room temperature	Approved
Resistance to Soldering Heat	200	J-STD-020	Tp=245 °C , tp=20-30 s, 3 times reflow	Approved
Electrical Parameters	10	Product specification	Room temperature	Approved