




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-11 @20°C	1.0 ohms max.
D.C. RESISTANCE	5-7 tie(5+6, 7+8), @20°C	0.4 ohms max.
INDUCTANCE	5-7 tie(5+6, 7+8), 10kHz, 100mVAC, Ls	200uH $\pm 10\%$
SATURATION CURRENT	20% rolloff from initial	6A min.
LEAKAGE INDUCTANCE	5-7 tie(5+6, 7+8, 2+11), 100kHz, 100mVAC, Ls	130uH max.
DIELECTRIC	5-2 tie(5+6), 960VAC, 1 second	800VAC, 1 minute
URNS RATIO	(5-7):(2-11)	10:1, $\pm 2\%$

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications Method: Tray PKG-0841 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13] Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750370081
6B	2/13		CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750370081	SPECIFICATION SHEET 1 OF 1
6A	7/11	SEE REVISION SHEET FOR REVISION LEVEL				

