




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

D.C. RESISTANCE (@20°C):	2-3 , 0.449 Ohms $\pm 10\%$. 4-5 , 0.290 Ohms $\pm 10\%$. 7-9 , 0.233 Ohms $\pm 10\%$.
DIELECTRIC RATING:	4500VAC, 1 minute tested by applying 4500VAC for 1 second between pins 2-9 (tie 3+4). 500VAC, 1 minute tested by applying 625VAC for 1 second between pins 2-5.
INDUCTANCE:	300 μ H $\pm 10\%$, 10kHz, 100mVAC, 0mADC, 2-3, Ls.
SATURATION CURRENT:	2.4A saturating current that causes 20% rolloff from initial inductance.
LEAKAGE INDUCTANCE:	4.0 μ H typ, 8.0 μ H max., 100kHz, 100mVAC, 2-3(tie 4+5, 7+9), Ls.
URNS RATIO:	(3-2):(5-4) , (3.75):(1.00) , $\pm 1\%$. (3-2):(9-7) , (3):(1.00) , $\pm 1\%$.

Designed to comply with the following requirements as defined by IEC61558-2-16:
- Reinforced insulation for a primary circuit at a working voltage of 400VDC.

OPERATING TEMPERATURE RANGE: -40°C to 125°C including temp. rise.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

WE-Midcom, Inc. Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$ Decimals: $\pm .005$ (.127mm)		WE-Midcom, Inc.	
	Drawing Title Transformer		Drawing Number 750815046	Rev. 02
This drawing is dual dimensioned. Dimensions in brackets are in millimeters	Revisions: See Sheet 1		Scale ----	Spec Sheet 1 of 1
Engineer:LJG			12/11/2012	