

#	Layer	Thickness	Description	Note
	Top Solder	0.015mm	Soldermask IPC-SM840	used on rigid parts
	Top Surface Finish	0.006mm		
1	Top Side	0.035mm	Starting foil 1/2oz. after plating and processing	
		0.370mm	Prepreg IPC-4101/127/128	FR-4.1 filled, halogen free
2	Inner Layer 1	0.017mm	ED Base Copper	
		0.510mm	Core IPC-4101/127/128	FR-4.1 filled, halogen free
3	Inner Layer 2	0.017mm	ED Base Copper	
		0.370mm	Prepreg IPC-4101/127/128	FR-4.1 filled, halogen free
4	Inner Layer 3	0.017mm	ED Base Copper	
		0.510mm	Core IPC-4101/127/128	FR-4.1 filled, halogen free
5	Inner Layer 4	0.017mm	ED Base Copper	
		0.370mm	Prepreg IPC-4101/127/128	FR-4.1 filled, halogen free
6	Bottom Side	0.035mm	Starting foil 1/2oz. after plating and processing	
	Bottom Surface Finish	0.006mm		
	Bottom Solder	0.015mm	Soldermask IPC-SM840	used on rigid parts

Total thickness: 2.309mm

notes:

Final copper thicknesses according to IPC-6012 **BASIC6_ML6_230_17_2V13**

Standard: Surface Finish ENIG
(Ni 5.5 µm ± 1.5 µm, Au 0.075 µm ± 0.025 µm)

PCB Thickness Tolerance: ± 10%			
customer		created	
pcb name		approved	
engineer		format	A4, landscape
date			

Please follow our sectional design rules:
► www.we-online.com/designrulesbasic_en

For impedance matching stackups: Please consult our specialists: BASIC@we-online.com

Template Revision: 10/2023 by Andreas Schilpp / Michael Kress / Werner Öchslen



**WÜRTH
ELEKTRONIK**
MORE THAN
YOU EXPECT