



#	Layer	Thickness	Description	Note
	Top Solder	0.015mm	Soldermask IPC-SM840	used on rigid parts
	Top Surface Finish	0.006mm		
1	Top Side	0.025mm	Starting foil 1/4oz. after plating and processing	
		0.030mm	Prepreg IPC-4101/127/128	FR-4.1 filled, halogen free
2	Inner Layer 1	0.025mm	Starting foil 1/4oz. after plating and processing	
		0.100mm	Core IPC-4101/127/128	FR-4.1 filled, halogen free
3	Inner Layer 2	0.025mm	Starting foil 1/4oz. after plating and processing	
		0.030mm	Prepreg IPC-4101/127/128	FR-4.1 filled, halogen free
4	Bottom Side	0.025mm	Starting foil 1/4oz. after plating and processing	
	Bottom Surface Finish	0.006mm		
	Bottom Solder	0.015mm	Soldermask IPC-SM840	used on rigid parts

Total thickness: 0.301mm

notes:

Standard: Only microvias, NO PTHs
With PTH Copper 35 µm thick on Top/Bottom

Standard: Surface Finish ENIG
(Ni 5.5 µm ± 1.5 µm, Au 0.075 µm ± 0.025 µm)

Final copper thicknesses according to IPC-6012

Please follow our sectional design rules:
► www.we-online.com/designruleslimhdi_en

HDI4_1-2b-1_030_25_2V13

PCB Thickness Tolerance: ± 10%

customer		created	
----------	--	---------	--

pcb name		approved	
----------	--	----------	--

engineer		format	A4, landscape
----------	--	--------	---------------

date			
------	--	--	--

Template Revision: 10/2023 by Andreas Schilpp / Michael Kress / Werner Öchslen



**WÜRTH
ELEKTRONIK**
MORE THAN
YOU EXPECT