



Product / Process Change Notification (PCN)

- Major Change
 Minor Change

PCN Number: PCN_WPME-FISM_1779205341_20250120

Affected Series: WPME-FISM

Affected Part Number: 1779205341

PCN Date: 2024-12-20 (YYYY-MM-DD)

Effective Date: 2025-01-20 (YYYY-MM-DD)

Change Category:

- Equipment/Location
 General Data
 Material
 Process
 Product Design
 Shipping/Packaging
 Supplier
 Software

Contact: Product Management

Phone: +49 (0) 7942 - 945 5001

Fax: +49 (0) 7942 - 945 5179

E-Mail: pcn.eisos@we-online.com

Datasheet Change:

Yes No

Attachment:

Yes No

DESCRIPTION OF CHANGE:

Due to an improvement of the production capability, Würth Elektronik eiSos has shifted the production of the affected part number to a new factory location.

With the aim of an extended product applicability, Würth Elektronik eiSos has updated the BOM used in the module to ensure the best performance and the electrical specifications.

There will be no change in fit or quality of the product.

The new revision of the affected part number will be sent out after the previous revision is out of stock (according to FIFO - first-in, first-out).

DETAILS OF CHANGE:

All changes indicated below apply to the part number in this PCN.

Previous production line	New production line
Lot number beginning with: 489xxxxxxxxxxx	Lot number beginning with: 676xxxxxxxxxxx
Country of origin: China	Country of origin: China



The part numbers of the FISM series are now distributed in single datasheets instead of the previous family datasheet approach

Before Change

1779205x41
Magi³C Power Module
 WPME-FISM - Fixed Isolated SIP/SMT Module

5V, 12V or 24V / 1W / 3kV Functional Isolated Unregulated 5V Output

DESCRIPTION

The FISM power module family is an unregulated, functional isolated, fully integrated DC/DC converter.

The module integrates the switching power stage, control circuitry, transformer and input/output capacitors.

The module requires no external components for operation thus reducing design effort and complexity to a minimum.

The FISM ensures fast time to market and low development costs.

The 1779205x41 series of the FISM family achieves typically an efficiency of 80% up to 86%.

The series is available in a SIP-7 package (19.65 x 6 x 10,16mm).

FEATURES

- 3kV DC functional isolation for 60s
- Continuous short-circuit protection
- Current capability up to 0.2A
- Nominal input voltage rails: 5V / 12V / 24V
- Output voltage: 5V unregulated
- No minimum load required
- Continuous output power: 1W
- Integrated C_{IN}, C_{OUT} and transformer
- Dynamic power boost up to 300mA for 0.5s
- Low output voltage ripple: Typ. 55mV at full load
- Output voltage accuracy: Typ. +3% / -2.5%
- Operating switching frequency: 300kHz (1779205141), 600kHz (1779205241, 1779205341)
- Operating ambient temperature range: -40°C to 105°C
- RoHS & REACH compliant
- Complies with EN56032 (CISPR-32) class B conducted and radiated emissions standard
- UL62368-1 approved

After Change

1779205341
Magi³C Power Module
 WPME-FISM - Fixed Isolated SIP/SMT Module

24V input / 1W / 4kV Functional Isolated / Unregulated 5V Output

DESCRIPTION

The FISM 1779205341 Magi³C power module is an unregulated, functionally isolated, fully integrated DC/DC converter.

The module integrates the switching power stage, control circuitry, transformer and input/output capacitors.

The module requires no external components for operation thus reducing design effort and complexity to a minimum.

The FISM module ensures fast time to market and low development costs.

The 1779205341 module achieves an efficiency up to 82%.

FEATURES

- 4kV DC functional isolation for 1s
- 3kV DC functional isolation for 60s
- Nominal input voltage rail: 24V
- Output voltage: 5V unregulated
- Low output voltage ripple: Typ. 55mV at full load
- Output voltage accuracy: Typ. -0.4% at full load
- Output power: 1W (0.2A)
- Dynamic power boost up to 0.3A for 0.5s
- Continuous short-circuit protection
- Isolation capacitance of typ. 20pF
- Integrated C_{IN}, C_{OUT} and transformer
- Operating ambient temperature range: -40°C to 105°C
- RoHS & REACH compliant
- Complies with EN55032 (CISPR-32) class B conducted and radiated emissions standard
- UL62368-1 recognized

The datasheet electrical specifications (absolute maximum / electrical) have been adjusted based on the new design.

Before Change

ABSOLUTE MAXIMUM RATINGS

Caution:
 Exceeding the listed absolute maximum ratings may affect the device negatively and may cause permanent damage. These are stress ratings only, which do not imply functional operation of the device at these or any other condition beyond those indicated under Operating Conditions.

SYMBOL	PARAMETER	LIMIT		UNIT	
		MIN ⁽¹⁾	MAX ⁽¹⁾		
VIN	Input pin voltage	5V _{IN} / 5V _{OUT} version,(1779205141)	-0.4	6	V
		12V _{IN} / 5V _{OUT} version,(1779205241)	-0.4	25	V
		24V _{IN} / 5V _{OUT} version,(1779205341)	-0.4	50	V
VOUT	Output pin voltage	5V _{IN} / 5V _{OUT} version,(1779205141)	-0.7	11	V
		12V _{IN} / 5V _{OUT} version,(1779205241)	-0.7	16	V
		24V _{IN} / 5V _{OUT} version,(1779205341)	-0.7	16	V
V _{ISO}	Isolation voltage input to output for 1s ⁽²⁾	-	4000	V	
		Isolation voltage input to output, tested 100% for 60s ⁽²⁾	-	3000	V
T _{storage}	Assembled, non-operating storage temperature	-55	125	°C	
V _{ESD}	ESD Voltage (HBM), according to EN61000-4-2 ⁽³⁾	-4	4	kV	

After Change

5 ABSOLUTE MAXIMUM RATINGS

Caution:
 Exceeding the listed absolute maximum ratings may affect the device negatively and may cause permanent damage.

Table 6: Absolute maximum ratings.

SYMBOL	PARAMETER	LIMIT		UNIT
		MIN ⁽¹⁾	MAX ⁽¹⁾	
VIN	Input pin voltage	-0.3	38	V
VOUT	Output pin voltage	-0.3	25	V
V _{ISO}	Isolation voltage input to output for 60s ⁽²⁾	—	3	kV
	Isolation voltage input to output, 100% tested for 1s ⁽¹⁾	—	4	kV
T _{storage}	Assembled, non-operating storage temperature	-55	125	°C
V _{ESD}	ESD Voltage (HBM), according to EN61000-4-2 ⁽³⁾	-4	4	kV



ELECTRICAL SPECIFICATIONS

MIN and MAX limits are valid for the recommended ambient temperature range of -40 °C to 105 °C. Typical values represent statistically the utmost probable values at the following conditions: $T_A = 25\text{ °C}$, unless otherwise noted.

SYMBOL	PARAMETER	TEST CONDITIONS	MIN ⁽¹⁾	TYP ⁽²⁾	MAX ⁽¹⁾	UNIT
Output Current						
I_{MOC}	Maximum overload current		-	-	300 ⁽⁷⁾	mA
Accuracy						
V_{OUT}	Line regulation	per 1.0% change in input voltage ⁽⁸⁾	-	-	1.2	%
	Load Regulation	V_{IN} nominal, $V_{OUT} = 5V$ $I_{OUT} = 20mA$ to $200mA$	-	10	-	%
	Output voltage accuracy	V_{IN} nominal, $I_{OUT} = 200mA$	-7.5	-	8	%
	Output voltage at no load	V_{IN} nominal	-	5.5	-	V
	Output voltage ripple & noise	V_{IN} nominal, $V_{OUT} = 5V$ 20MHz BWL	-	55	-	mV _{pp}
Switching Frequency						
f_{SW}	Switching frequency	$V_{IN} = 5V$, $I_{OUT} = 200mA$ (1779205141)	-	300	-	kHz
		$V_{IN} = 12V$, $I_{OUT} = 200mA$ (1779205241)	-	600	-	kHz
		$V_{IN} = 24V$, $I_{OUT} = 200mA$ (1779205341)	-	600	-	kHz
Input Current						
I_{IN}	No load input current (operating, switching)	$V_{IN} = 5V$, $I_{OUT} = 0mA$ (1779205141)	-	11	-	mA
		$V_{IN} = 12V$, $I_{OUT} = 0mA$ (1779205241)	-	3	-	mA
		$V_{IN} = 24V$, $I_{OUT} = 0mA$ (1779205341)	-	3	-	mA
Efficiency						
η	Efficiency	$V_{IN} = 5V$, $I_{OUT} = 200mA$ (1779205111)	-	85	-	%
		$V_{IN} = 12V$, $I_{OUT} = 200mA$ (1779205241)	-	85	-	%
		$V_{IN} = 24V$, $I_{OUT} = 200mA$ (1779205341)	-	80	-	%
Isolation Characteristics						
C_{ISO}	Isolation capacitance	100kHz/0.1V	-	20	-	pF
R_{ISO}	Isolation resistance	500VDC	1	-	-	GΩ

8 ELECTRICAL SPECIFICATIONS

Caution:
 MIN and MAX limits are valid for the recommended ambient temperature range of -40 °C to 105 °C. Typical values represent statistically the utmost probable values at the following conditions: $T_A = 25\text{ °C}$, unless otherwise noted.

Table 9: Electrical specifications.

SYMBOL	PARAMETER	TEST CONDITIONS	MIN ⁽¹⁾	TYP ⁽²⁾	MAX ⁽¹⁾	UNIT
Output Current						
I_{MOC}	Maximum overload current		-	-	0.3 ⁽⁸⁾	A
Accuracy						
V_{OUT}	Line regulation	per 1.0% change in input voltage ⁽⁸⁾	-	1.2	-	%
	Load Regulation	V_{IN} nominal, $V_{OUT} = 5V$ $I_{OUT} = 0.02A$ to $0.2A$	-	10	15	%
	Output voltage accuracy	V_{IN} nominal, $I_{OUT} = 0.2A$	-	-0.4	-	%
	Output voltage at no load	V_{IN} nominal	-	5.5	-	V
	Output voltage ripple & noise	V_{IN} nominal, $V_{OUT} = 5V$ 20MHz BWL	-	55	-	mV _{pp}
Switching Frequency						
f_{SW}	Switching frequency, internal clock	V_{IN} nominal, $I_{OUT} = 0.2A$	-	240	-	kHz
	Switching frequency, input current	V_{IN} nominal, $I_{OUT} = 0.2A$	-	480 ⁽¹⁰⁾	-	kHz
Input Current						
I_{IN}	No load input current	$V_{IN} = 24V$, $I_{OUT} = 0A$	-	3.1	-	mA
Efficiency						
η	Efficiency	$V_{IN} = 24V$, $I_{OUT} = 0.2A$	-	82	-	%
Isolation Characteristics						
C_{ISO}	Isolation capacitance	100kHz/0.1V	-	20	-	pF
R_{ISO}	Isolation resistance	500VDC	1	-	-	GΩ

Due to the change in production line the isolation voltage test specification has changed. The modules are now 100% production tested for 1 second. Therefore, the specified isolation voltage has been increased to the 1 second value.

Before Change	After Change
<p>3.3V, 5V, 12V or 24V Input / 1W 3kV Functional Isolated / Unregulated 5V Output</p> <p>DESCRIPTION</p> <p>The FISM 1769205x41 MagPiC power module series are unregulated, functionally isolated, fully integrated DC/DC converters.</p> <p>The modules integrate the switching power stage, control circuitry, transformer and input/output capacitors.</p> <p>The modules require no external components for operation thus reducing design effort and complexity to a minimum.</p> <p>The FISM family ensures fast time to market and low development costs.</p> <p>The 1769205x41 series of the FISM family achieves an efficiency of 84% to 90.5%.</p> <p>The series is available in an SMT-8 package (13.2 x 11.4 x 7.25)mm.</p> <p>FEATURES</p> <ul style="list-style-type: none"> • 3kV DC functional isolation for 60s • Nominal input voltage range: 3.3V / 5V / 12V / 24V • Output voltage: 5V unregulated • Low output voltage ripple: Typ. 55mV at full load • Output voltage accuracy: Typ. -2.5% at full load • Output power: 1W (0.2A) • Dynamic power boost up to 0.3A for 0.5s • Continuous short-circuit protection • Isolation capacitance of typ. 20pF • Integrated C_{IN}, C_{OUT} and transformer • Operating ambient temperature range: -40 °C to 105 °C • RoHS & REACH compliant • Complies with EN55032 (CISPR-32) class B conducted and radiated emissions standard • UL62368-1 approved 	<p>24V Input / 1W 4kV Functional Isolated / Unregulated 5V Output</p> <p>DESCRIPTION</p> <p>The FISM 1779205341 MagPiC power module is an unregulated, functionally isolated, fully integrated DC/DC converter.</p> <p>The module integrates the switching power stage, control circuitry, transformer and input/output capacitors.</p> <p>The module requires no external components for operation thus reducing design effort and complexity to a minimum.</p> <p>The FISM module ensures fast time to market and low development costs.</p> <p>The 1779205341 module achieves an efficiency up to 82%.</p> <p>FEATURES</p> <ul style="list-style-type: none"> • 4kV DC functional isolation for 1s • 3kV DC functional isolation for 60s • Nominal input voltage rail: 24V • Output voltage: 5V unregulated • Low output voltage ripple: Typ. 55mV at full load • Output voltage accuracy: Typ. -0.4% at full load • Output power: 1W (0.2A) • Dynamic power boost up to 0.3A for 0.5s • Continuous short-circuit protection • Isolation capacitance of typ. 20pF • Integrated C_{IN}, C_{OUT} and transformer • Operating ambient temperature range: -40 °C to 105 °C • RoHS & REACH compliant • Complies with EN55032 (CISPR-32) class B conducted and radiated emissions standard • UL62368-1 recognized



5 ABSOLUTE MAXIMUM RATINGS					
Caution: Exceeding the listed absolute maximum ratings may affect the device negatively and may cause permanent damage.					
Table 5: Absolute maximum ratings.					
SYMBOL	PARAMETER	LIMIT		UNIT	
		MIN ⁽¹⁾	MAX ⁽¹⁾		
VIN	Input pin voltage	3.3V _{IN} / 5V _{OUT} version (1769205041)	-0.4	9	V
		5V _{IN} / 5V _{OUT} version (1769205141)	-0.4	10	V
		12V _{IN} / 5V _{OUT} version (1769205241)	-0.4	16	V
		24V _{IN} / 5V _{OUT} version (1769205341)	-0.4	50	V
VOUT	Output pin voltage	3.3V _{IN} / 5V _{OUT} version (1769205041)	-0.7	16	V
		5V _{IN} / 5V _{OUT} version (1769205141)	-0.7	16	V
		12V _{IN} / 5V _{OUT} version (1769205241)	-0.7	25	V
		24V _{IN} / 5V _{OUT} version (1769205341)	-0.7	16	V
		V _{ISO}	Isolation voltage input to output for 1s ⁽²⁾	—	4
	Isolation voltage input to output, 100% tested for 60s ⁽²⁾	—	3	kV	
T _{storage}	Assembled, non-operating storage temperature	-55	125	°C	
V _{ESD}	ESD Voltage (HBM), according to EN61000-4-2 ⁽³⁾	-4	4	kV	

5 ABSOLUTE MAXIMUM RATINGS				
Caution: Exceeding the listed absolute maximum ratings may affect the device negatively and may cause permanent damage.				
Table 6: Absolute maximum ratings.				
SYMBOL	PARAMETER	LIMIT		UNIT
		MIN ⁽¹⁾	MAX ⁽¹⁾	
VIN	Input pin voltage	-0.3	38	V
VOUT	Output pin voltage	-0.3	25	V
V _{ISO}	Isolation voltage input to output for 60s ⁽²⁾	—	3	kV
	Isolation voltage input to output, 100% tested for 1s ⁽²⁾	—	4	kV
T _{storage}	Assembled, non-operating storage temperature	-55	125	°C
V _{ESD}	ESD Voltage (HBM), according to EN61000-4-2 ⁽³⁾	-4	4	kV

The datasheet MTBF specifications have been adjusted based on the new internal design.

Before Change					After Change				
RELIABILITY					12 RELIABILITY				
Table 13: Reliability.					Table 13: Reliability.				
SYMBOL	PARAMETER	TEST CONDITIONS	TYP ⁽³⁾	UNIT	SYMBOL	PARAMETER	TEST CONDITIONS	TYP ⁽³⁾	UNIT
MTBF ⁽³⁾	Mean Time Between Failures	+25°C: Ground Benign	5200 · 10 ³	h	MTBF ⁽¹¹⁾	Mean Time Between Failures	+25°C: Ground Benign	7057 · 10 ³	h
		+100°C: Ground Benign	950 · 10 ³	h			+85°C: Ground Benign	2282 · 10 ³	h


The diagrams shown in chapter TYPICAL PERFORMANCE CURVES are updated based on new electrical specifications. The used test conditions stay the same as before.

Due to internal BOM change the recommendation for the filter components to comply with EN55032 have been adjusted.

Before Change							After Change						
19.3 Bill of Materials							19.3 Bill of Materials						
Table 14: Design example bill of materials.							Table 14: Design example bill of materials.						
DESIGNATOR	DESCRIPTION	FUNCTION	QUANTITY	ORDER CODE	MANUFACTURER	DESIGNATOR	DESCRIPTION	FUNCTION	QUANTITY	ORDER CODE	MANUFACTURER		
U1	Mag ³ C Power Module	Power supply	1	1779205341	WE	U1	Mag ³ C Power Module	Power supply	1	1779205341	WE		
L ₁	Filter inductor, 1µH, PD2 family, I _{sat} = 5.72A, I ₀ = 4A	Input Filter	1	7447730	WE	L ₁	Filter inductor, 1µH, PD2 family, I _{sat} = 5.72A, I ₀ = 4A	Input Filter	1	7447730	WE		
C ₁	Ceramic chip capacitor 4.7µF/50V X7R, 1210	Input Filter	1	885012209048	WE	C ₁	Ceramic chip capacitor 4.7µF/50V X7R, 1210	Input Filter	1	885012209048	WE		
C ₂	Ceramic chip capacitor 4.7µF/50V X7R, 1210	Input Filter / Electrical Performance	1	885012209048	WE	C ₂	Ceramic chip capacitor 4.7µF/50V X7R, 1210	Input Filter / Electrical Performance	1	885012209048	WE		
C ₃	Ceramic chip capacitor 10µF/16V X7R, 1210	Output Filter / Electrical Performance	1	885012109009	WE	C ₃	Ceramic chip capacitor 10µF/16V X7R, 1210	Output Filter / Electrical Performance	1	885012109009	WE		
C ₄	Ceramic chip capacitor 470pF/250Vac/3kV 1812 X7R	Y-Cap	1	8853522110011	WE	C ₄	Ceramic chip capacitor 1nF 3kV 1812 X7R	Y-Cap	1	8853422110009	WE		

The modules still are based on either a full bridge or a push-pull topology. In some cases the single part number topology switched from previous full bridge topology to a push-pull topology or vice versa. The topology change is indicated in the BLOCK DIAGRAM chapter.

Before Change




CIRCUIT DESCRIPTION

The Mag¹C power module 1779205141 is based on full bridge topology whereas the Mag¹C power modules 1779205341 / 1779205341 are based on a push-pull converter. All modules have an integrated IC, rectifying diodes, input and output capacitors and a transformer.

Since there is no feedback path from the output to the input, the duty cycle is fixed at 50% and is independent of the load (zero load to full load). The output voltage is unregulated and defined by the turns ratio of the transformer.

After Change



17 CIRCUIT DESCRIPTION

The Mag¹C power module 1779205341 is based on a full bridge topology. The module has an integrated IC, rectifying diodes, input and output capacitors and a transformer.

Since there is no feedback path from the output to the input, the duty cycle is fixed at 50% and is independent of the load (zero load to full load). The output voltage is unregulated and defined by the turns ratio of the transformer.

The handling recommendations for the wave solder profile have been expanded to include the maximum allowable time for each wave.

Before Change

18.1 Solder Profile

Table 10: Wave solder profile.

Profile Feature	Old standard (Pb)	New (Pb-free)
Time within peak temperature t_p	10s	10s
Average ramp-up rate between T_s and T_p	200°C/s	200°C/s
Final preheat temperature T_s	130°C/s	130°C/s
Peak temperature T_p	+235°C/s	+260°C/s
Ramp-down rate	-5°C/s	-5°C/s
Heating rate during preheat	4°C/s	4°C/s


After Change

19.1 Soldering Profile


Table 12: Wave solder profile.

Profile Feature	Old standard (Pb)	New (Pb-free)
Time within peak temperature t_p	max. 10s max. 5s each wave	max. 10s max. 5s each wave
Average ramp-up rate	200°C/s	200°C/s
Final preheat temperature T_s	130°C/s	130°C/s
Peak temperature T_p	+235°C/s	+260°C/s
Ramp-down rate	-5°C/s	-5°C/s
Heating rate during preheat	4°C/s	4°C/s

The mechanical dimensions have been updated based on new production. SIP-7 package shapes stay the same but with slightly deviated package length and height.



The packaging specifications have been adjusted.





RELIABILITY / QUALIFICATION OF CHANGE:				
An additional reliability testing was performed and approved. Sample size is valid for every single partnumber stated in this PCN unless otherwise noted.				
Additional details of the tests can be found in the table below:				
Test Item	Sample Size	Reference	Test Conditions	Acceptance
Temperature Cycling	25	JESD22 Method JA-104	Temperature: -40 °C to 85 °C Testing Time: 500 cycles Test Cycles/h: 3 Min. soak time: 1 min	Approved
Electrical Characterization	30	User Spec.	Measure electrical DC performance @25 °C, - 40 °C, 105 °C Transient performance tests @25 °C Thermal derating measurement.	Approved
Low Temperature Storage Life	25	JESD22-A119	500hrs @ -40 °C	Approved
High Temperature Storage Life	25	JESD22-A119	500hrs @ 125 °C	Approved
Steady State Humidity	25	MIL-STD-202, Method 106	Temperature: 65± 2 °C Testing Time: 504h Humidity: 95%RH	Approved
High Pot Test	5	UL62368-1	Specified isolation voltage value tested for 60s. Given design parameter tested for 1s	Approved
Mechanical Shock	30	MIL-STD-202-213	3 shocks in each direction (x, -x, y, -y, z, -z), peak value of 100 g, duration 6 ms, half-sine, velocity change 12.3 ft/s.	Approved
Vibration	30	MIL-STD-202-204	5 g for 20 min, 12 cycles each of 3 orientations. Test from 10 Hz to 2000 Hz.	Approved