

#	Layer	Thickness	Description	Note
	Top Solder	0.015mm	Soldermask IPC-SM840	used on rigid parts
	Top Surface Finish	0.006mm		
1	Top Side	0.035mm	Starting foil 1/2oz. after plating and processing	
		0.370mm	Prepreg IPC-4101/127/128	FR-4.1 filled, halogen free
2	Inner Layer 1	0.035mm	ED Base Copper	
		0.510mm	Core IPC-4101/127/128	FR-4.1 filled, halogen free
3	Inner Layer 2	0.035mm	ED Base Copper	
		0.370mm	Prepreg IPC-4101/127/128	FR-4.1 filled, halogen free
4	Inner Layer 3	0.035mm	ED Base Copper	
		0.510mm	Core IPC-4101/127/128	FR-4.1 filled, halogen free
5	Inner Layer 4	0.035mm	ED Base Copper	
		0.370mm	Prepreg IPC-4101/127/128	FR-4.1 filled, halogen free
6	Bottom Side	0.035mm	Starting foil 1/2oz. after plating and processing	
	Bottom Surface Finish	0.006mm		
	Bottom Solder	0.015mm	Soldermask IPC-SM840	used on rigid parts

Total thickness: 2.381mm

notes:

Final copper thicknesses according to IPC-6012

Standard: Surface Finish ENIG
(Ni 5.5 µm ± 1.5 µm, Au 0.075 µm ± 0.025 µm)

Please follow our sectional design rules:
► www.we-online.com/designrulesbasic_en

For impedance matching stackups: Please consult our specialists: BASIC@we-online.com

BASIC6_ML6_238_35_2V13

PCB Thickness Tolerance: ± 10%

customer	created
pcb name	approved
engineer	format
date	A4, landscape

Template Revision: 10/2023 by Andreas Schilpp / Michael Kress / Werner Öchslen



**WÜRTH
ELEKTRONIK**
MORE THAN
YOU EXPECT