

Rigid


# Layer	Thickness	Description	Note
Top Solder	0.015mm	Soldermask IPC-SM840	used on rigid parts
Top Surface Finish	0.006mm		
1 Top Side	0.040mm	Starting foil 1/4oz. after plating and processing	
	0.050mm	Flexible core IPC-4204/11	Flex Polyimide adhesiveless
	0.050mm	Prepreg IPC-4101/127/128	LowFlow FR-4.1 filled, halogen free
2 Inner Layer 1	0.017mm	ED Base Copper	
	1.165mm	Core IPC-4101/127/128 w/o Cu 0.5 oz.	FR-4.1 filled, halogen free
3 Inner Layer 2	0.017mm	ED Base Copper	
	0.090mm	Prepreg IPC-4101/127/128	FR-4.1 filled, halogen free
4 Bottom Side	0.040mm	Starting foil 1/4oz. after plating and processing	
Bottom Surface Finish	0.006mm		
Bottom Solder	0.015mm	Soldermask IPC-SM840	used on rigid parts
Total thickness: 1.510mm			

notes:		FLEX4_1F-3Ri_151_17_2V13	
Final copper thicknesses according to IPC-6013	Please follow our sectional design rules: ▶ www.we-online.com/designrigidflex	PCB Thickness Tolerance: rigid ± 10% / flex ± 0,05mm	
IPC-2223 use A "Flex to install"	For impedance matching stackups: Please consult our specialists: FLEX@we-online.com	customer	created
Standard: Surface Finish ENIG (Ni 5.5 µm ± 1.5 µm, Au 0.075 µm ± 0.025 µm)		pcb name	approved
		engineer	format A4, landscape
		date	
Template Revision: 10/2023 by Andreas Schilpp / Michael Kress / Werner Öchslen			




**WÜRTH
ELEKTRONIK**
MORE THAN
YOU EXPECT

Flex



# Layer	Thickness	Description	Note
Flex Top Flexible Soldermask	0.040mm	Soldermask JIS-C-5012/IPC-SM840	flexibel, thermal cured
1 Top Side	0.040mm	Starting foil 1/4oz. after plating and processing	
	0.050mm	Flexible core IPC-4204/11	Flex Polyimide adhesiveless
Total thickness: 0.130mm			

notes:		FLEX4_1F-3Ri_151_17_2V13		 WÜRTH ELEKTRONIK MORE THAN YOU EXPECT
Final copper thicknesses according to IPC-6013	Please follow our sectional design rules: ▶ www.we-online.com/designrigidflex	PCB Thickness Tolerance: rigid ± 10% / flex ± 0,05mm		
IPC-2223 use A "Flex to install"	For impedance matching stackups: Please consult our specialists: FLEX@we-online.com	customer	created	
Standard: Surface Finish ENIG (Ni 5.5 µm ± 1.5 µm, Au 0.075 µm ± 0.025 µm)		pcb name	approved	
		engineer	format A4, landscape	
		date		
Template Revision: 10/2023 by Andreas Schilpp / Michael Kress / Werner Öchslen				