

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:




PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	3.68 ohms ±10%
D.C. RESISTANCE	4-3 @20°C	3.68 ohms ±10%
INDUCTANCE	1-2 10kHz, 100mVAC, Ls	91mH -30%/+50%
INDUCTANCE	4-3 10kHz, 100mVAC, Ls	91mH -30%/+50%
SATURATION CURRENT	tie(2+3), 20% rolloff from initial	0.95A
LEAKAGE INDUCTANCE	tie(2+3), 10kHz, 100mVAC, Ls	4.12mH typ.
DIELECTRIC	1-4 3125VAC, 1 second	2500VAC, 1 minute
TURNS RATIO	(1-2):(4-3)	1:1, ±1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

RATED CURRENT: 350mA causes 40°C temp rise from ambient.

- Ⓞ Designed to comply with IEC60938-2 for 250VACrms or VDC.
- Ⓞ Designed to comply with UL 1283 for 300Vrms, 424.3Vpeak.
- Ⓞ Designed to comply with UL 1993 for 347VACrms or VDC.



Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications Method: Tray PKG-1012 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [1.3] Footprint: ±.001 [1.03]	DRAWING TITLE <b>FILTER</b> COMMON MODE CHOKE	PART NO. <b>750314400</b>
6C	8/15			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750314400	
6B	1/15					
6A	10/14	SEE REVISION SHEET FOR REVISION LEVEL				SPECIFICATION SHEET 1 OF 1

